




C2G
3.3ft (1m) LC-LC 9/125 OS2 Duplex Single-Mode PVC Fiber Optic Cable (TAA Compliant) - Yellow
Part No. CG-29191



Cost-effective solution that provides high bandwidth and transmission rates over longer distances. With LC to LC termination, this high quality fiber optic patch cable is specifically designed for gigabit ethernet applications. The patented injection molding process provides each connection greater durability in resisting pulls, strains and impacts from cabling installs.

Each cable is 100% optically inspected and tested for insertion loss before you receive it. A pull-proof jacket design surrounds the popular 9/125 Single-mode fiber, immune to electrical interference.

Features & Benefits

Designed to support gigabit ethernet applications

Patented injection molding process for greater durability

Optically inspected and tested for insertion loss

Pull-proof jacket design, immune to electrical interference

Specifications

General Info

Product Line	C2G	Color	Yellow
UPC Number	757120291916	Country Of Origin	China
Application Sector	Commercial, Industrial	Warranty Type	Lifetime
Type	Cable		

Dimensions

Product Length US	3.3 FT	Cable Length	3.3 ft
-------------------	--------	--------------	--------

Technical Information

Fiber Optic Cable Type	Single-Mode, OS2	Jacket Material	PVC (Polyvinyl Chloride)
Jacket Application	Riser Rated	Bend Radius	50 mm
Simplex/Duplex	Duplex	Cable Type	Fiber Optic
Jacket Rating	FT4 Rated, OFNR Rated	Adapter Rear	LC Male
Adapter Front	LC Male	Fiber Size	9/125