

SFERA PRO

USB Microphone

The Sfera Pro is a studio-quality microphone designed for streaming and gaming in style. The USB connection cord allows users to simply 'Plug-in & Play' for an easier set up on PCs, Macs, and popular gaming consoles. In comparison to the Sfera, the Sfera Pro offers switchable pickup settings for more diverse recording by adding Cardioid -10dB and Omnidirectional for those who want to add more presence to their recording. The Sfera Pro can also be placed on top your desk on an adjustable stand or attached to your microphone boom mount for varying uses.



FEATURES

- High-quality condenser capsule technology with switchable pickup patterns (Cardioid, Cardioid -10dB, and Omnidirectional)
- Adjustable stand
- 3.5 mm headphone jack with volume controller
- Mute button
- 5/8 inch thread mount
- Custom design USB cable and cable clip

SPECIFICATIONS

Polar Pattern	Cardioid, Cardioid -10dB, Omnidirectional
Frequency Response	20Hz – 20kHz
Capsule	2 high quality 14mm condenser capsules
Sample Rate	44.1kHz or 48kHz
Bit Depth	16bit
Maximum SPL	120dB (THD: 1% 1kHz)
Power	USB (5V 500mA)
Headphone Jack	3,5mm
Headphone Frequency Response	15Hz – 22kHz
Headphone Output	130mW
Controls	Pattern selector, Headphone volume controller, Mute button.

LOGISTIC

Netto Weight	kg	lbs	
Gross Weight	1kg	lbs	
Box Dimension	27,5x11,2x23,8cm	inches	
per pallet	224 pcs		
SKU/EAN	Black:	SFERA-PRO-BLACK	0769498678848
	Silver:	SFERA-PRO-SILVER	0769498678855