

Combat Cyber Security Threats



Secure KVM Switch Series

Ensure High-Level Security, Protection & Data Safekeeping

IOGEAR's new Secure KVM Switches are certified with the latest NIAP/ Common Criteria for Peripheral Sharing Switch Protection Profile v3.0 to provide maximum information security while sharing a single keyboard, mouse, speaker set and CAC reader.

Control up to 8 computers and utilize single or dual-video models with up to 4K UHD quality.



Desktop Security

- NIAP-CERTIFIED PP3.0**
Validated to Protection Profile for Peripheral Sharing Switches v3.0
- CAC AND BIOMETRICS SUPPORT**
Dedicated Peripheral Port for Authorized (White List) CAC Readers Only and Supported Biometrics Readers*
- CONTROLLED USB**
Admin Configurable Port Authentication Utility Secures USB Port Access
- PORT SELECTION VIA PUSH-BUTTON FOR ENHANCED SECURITY**
Keyboard Restrictions – OSD & Hotkey Methods are Not Allowed
- ISOLATED CHANNEL PER PORT**
Unidirectional Data Flow Restricts Leakage Between Connected Computers
- CLEARs KEYBOARD BUFFER**
Data Clears Automatically After Transmission to Switch and Reset

Active Tamper-Proof System

- ACTIVE CHASSIS INTRUSION DETECTION**
Compromising the Unit's Cover Renders it Inoperable
- TAMPER-EVIDENT SEALS**
Visually Detect Attempts to Gain Access to Switch's Internal Components
- TAMPER-PROOF HARDWARE**
Integrated Circuits are Soldered Directly Onto Board to Hinder Component Sabotage
- NON-REPROGRAMMABLE FIRMWARE**
Prevents Tampering and Attempts to Reprogram Switch's Firmware
- RUGGED METAL ENCLOSURE**
Durable, Full Metal Chassis

Superior Video Quality, Versatile Selection

- 2-, 4- and 8-Port Single & DUAL-VIEW**
One USB Console Securely Controls up to 8 Computers
- SUPERIOR 4K UHD VIDEO RESOLUTION**
Single or Dual-Link Resolution up to 3840 x 2160@30Hz
- VIDEO EDID™**
Eliminates Boot-Up Display Issues, Optimizes Resolution When Port Switching
- VERSATILE VIDEO CONNECTIONS**
Connect DisplayPort, DVI or HDMI Computers to HDMI or DVI Console Video
- ANALOG SPEAKER SUPPORT**
Secure Audio Data Input Does Not Convert Digital Audio to Analog Audio
- MULTI-PLATFORM SUPPORT**
Windows® 2000/Vista/7/8.1/10, Linux®, Mac® OS, & Sun®


* Compatible with Microsoft® LifeCam HD-3000 and Microsoft® Fingerprint Reader

Consolidate Multiple Workstations of Varying Security Classifications

		Secure KVM Switch Series - PP3.0								
PC Video Connection		DisplayPort			HDMI			DVI		
Console Video Connection		HDMI			HDMI			DVI		
Number of Ports		2	4	8	2	4	8	2	4	8
Resolution		3840 x 2160 @30Hz (UHD)			3840 x 2160 @30Hz (UHD) 1920 X 1080 (FHD)			3840 x 2160 @30Hz (UHD)* 2560 X 1600 DVI Dual-Link 1920 x 1200 DVI Single-Link 2048 x 1536 DVI-A		
Number of Displays	Single View	GCS1412TAA3	GCS1414TAA3	GCS1418TAA3	GCS1312TAA3	GCS1314TAA3	GCS1318TAA3	GCS1212TAA3	GCS1214TAA3	GCS1218TAA3
	Dual View	GCS1422TAA3	GCS1424TAA3	GCS1428TAA3	GCS1322TAA3	GCS1324TAA3	GCS1328TAA3	GCS1222TAA3	GCS1224TAA3	GCS1228TAA3
CAC Function		Yes								
Switching Method		Push-Button								
Keyboard/Mouse		USB; PS/2								
Speaker (analog)		Yes								
Microphone		No								
Tamper-proof		Yes								
Warranty		4 Years								
Number of Cable Sets Needed		6 Ft. USB KVM Cable Kit with Audio								
Number of Ports		2	4	8	2	4	8	2	4	8
Number of Displays	Single View	G2L902UTAA3	G2L902UTAA3	G2L902UTAA3	G2L802UTAA3	G2L802UTAA3	G2L802UTAA3	G2L702UTAA3	G2L702UTAA3	G2L702UTAA3
	Dual View	G2L9202UTAA3	G2L9202UTAA3	G2L9202UTAA3	G2L8202UTAA3	G2L8202UTAA3	G2L8202UTAA3	G2L7202UTAA3	G2L7202UTAA3	G2L7202UTAA3

*DVI Secure KVM Switches offer 3840 x 2160 @30Hz video output on compatible HDMI-interfaced monitors/computers with IOGEAR HDMI-to-DVI KVM Cables G2L7H02UTAA3

IOGEAR offers a wide range of TAA compliant products including CAC readers, combo keyboard + CAC readers, KVM/KVMPs, docking stations, wired/wireless AV, computer accessories, and cables.



For more info visit www.iogear.com/taa
Toll-Free: 866-9-IOGEAR (866-496-4327)
Govinfo@iogear.com