

EZCLEAN™ KC 1000



Models may vary from the image shown

CHERRY'S EZCLEAN™ KC 1000 keyboard features a smooth silicone cover that's easy to clean with most standard medical cleansers and disinfectant wipes while providing an exceptional tactile feel. Traditional keyboards, and even some sealed, anti-microbial keyboards are vulnerable to germs and bacteria, especially in hard to clean areas. The EZCLEAN™ KC 1000 keyboard... just type and wipe.

Applications include mobile medical carts, patient rooms, nurse stations, triage stations, labs and high traffic areas with multiple users.

Key Benefits

- Whisper quiet keys
- Ideal for medical cart and mobile applications
- Designed for continuous usage over 10 million confirmations per key
- Easy to clean surface that stands up to common cleaning solutions [see cleaning material listing below]
- Complete functions of a standard keyboard
- Can be used with the standard drivers of the operating system
- High level of reliability and precise tactile feedback

Technical Data:

• Do not use the following fluids or actions to clean the keyboard:

NO Petroleum based cleaning fluids, such as Gasoline (Petrol), Turpentine, or Oil,

NO Acetone.

NO cleaning fluid with over 10% bleach,

NO temperature sterilization,

NO abrasive scrubbing pads

• Suggested cleaning/disinfectant materials are:

Alcohol based cleaning products,

Chlorine bleach disinfectant wipes products,

10% Bleach solution,

10% Hydrogen Peroxide,

Disinfectant wipes,

Soap and water

Layout (country or language):

(possible country/layout versions, others available on request) US English with EURO symbol

Housing Color:

Product dependant, see table "Models"

Kev Color:

Product dependant, see table "Models"

Weight (product):

approx. 715 g /1.58 lb

Total Weight (with packaging):

approx. 1122 g / approx. 2.47 lb

Cable Length:

approx. 1.80 m / approx. 5.91 ft

Storage Temperature:

-20°C to 60°C / -4° F to 140° F

Operating Temperature:

0°C to 50°C / 32° F to 122° F

Current Consumption:

max. 100 mA

Interface:

• USB

Product Approvals:

• C-Tick
• UL
• CE
• FCC
• BSMI
• KCC
• TÜV-Süd/GS

System Requirements:

USB connection

Box Contents:

Product dependant, see table "Models"

Dimensions (product):

462 x 174 x 19 mm / 18.2 x 6.9 x 0.75 in

Packaging Dimensions:

501.7 x 244.6 x 50.8 mmm / 19.75 x 9.63 x 2 in

Reliability:

Product dependant, see table "Models"

Keyboard:

- Key Technology: LPK
- Service life, standard key: > 10 million key operations
- Number of Keys: 104+4
- Number of Additional Keys: 4

Packaging Unit:

- Number of products in the master package: 10
- Number of master packages per pallet: 16

Warranty:

Product dependant, see table "Models"

Errors, technical changes and delivery delays may occur. Technical information refers only to the specifications of the products. Features may differ from the information provided.



Models:

(possible country/layout versions, others available on request)

	Product Name	Order Number	Housing Color	Key Color	Warranty	Box Contents	Reliability
1	EZCLEAN™ KC 1000	EZN-0800EU- 0	white	white	2 years	Operating instructions in hard copy, EZClean® silicone cover, KC 1000 (JK-0800EU-0) keyboard	MTBF (90) > 80,000 hours
2	EZCLEAN™ KC 1000	EZN-0800EU- 2	black	black	2 years	Operating instructions in hard copy, EZClean® silicone cover, KC 1000 (JK-0800EU-2) keyboard	MTBF (90) > 80,000 hours
3	EZClean® Cover	KBCF0800N			1 Year Limited	EZClean® silicone cover	Cover Silicone life > 3 million key operations