

ThinkPad L580 20LW0010++

Region
EMEA

Machine Type
20LW

TopSeller
TopSeller

Processor
Core i7-8550U (4C, 1.8 / 4.0GHz, 8MB)

vPro
No

Graphics
Integrated Intel UHD Graphics 620

Memory
16GBx1

Display
15.6" FHD (1920x1080) IPS

Multi-touch
None

Storage
512GB SSD M.2 PCIe NVMe Opal2

Optical
None

WLAN + Bluetooth
Intel 8265 ac, 2x2 + BT4.1

WWAN
Fibocom L830-EB

SIM Card
None

Smart Card Reader
Smart Card Reader

Monitor Cable
None

Camera
720p

Keyboard
Backlit

Fingerprint Reader
Fingerprint Reader

NFC
None

TPM
dTPM 2.0

Battery
45Wh

Power Adapter
65W USB-C

Operating System
Windows 10 Pro 64

Warranty
1-year, Depot

End of Support
Feb 6, 2023

Ann Date (mm/yy)
02/18

Note:

Country Code "US" is for United States, "++" is for EMEA countries (e.g. AD - Saudi, Arabia, AT - Austria, BM - Bulgaria, etc.), "xx" is for EAST countries (e.g. BM - Bulgaria, CX - Hungary, CY - Cyprus, etc.), and "***" is for MEA countries (e.g. AD - Saudi, Arabia, ED - Egypt, EQ - Sweden, etc.). Please be aware that the EMEA/ EAST/MEA models listed above might not be available in all countries

 www.lenovo.com

This publication was developed for products and services offered in the United States and E.M.E.A countries. Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<http://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2018. All rights reserved.



Lenovo™

ThinkPad L580 Platform Specifications

Product Specifications Reference (PSREF)



Processor	Intel® Celeron® Processor, 7th Generation Intel Core™ i3 / i5 Processor (i3-7130U is NOT available in EMEA) or	Dimensions Weight Case color Case material	<i>WxDxH:</i> 14.82" x 10.02" x 0.90"; 376.5mm x 254.5mm x 22.95mm Starting at 4.46 lb / 2.0 kg Black PC/ABS plastic																																	
	<table border="1"> <thead> <tr> <th>Processor Number</th> <th># of Cores</th> <th># of Threads</th> <th>Base Frequency</th> <th>Max Turbo Frequency</th> <th>Cache</th> <th>Memory Types</th> <th>Processor Graphics</th> </tr> </thead> <tbody> <tr> <td>Cel 3965U</td> <td rowspan="2">2</td> <td rowspan="2">2</td> <td>2.2 GHz</td> <td>-</td> <td>2MB</td> <td rowspan="2">DDR4-2133</td> <td>Intel HD Graphics 610</td> </tr> <tr> <td>i3-7130U</td> <td>2.7 GHz</td> <td>-</td> <td>3MB</td> <td>Intel HD Graphics 620</td> </tr> <tr> <td>i5-7200U</td> <td rowspan="2">4</td> <td rowspan="2">4</td> <td>2.5 GHz</td> <td>3.1 GHz</td> <td>3MB</td> <td rowspan="2"></td> <td rowspan="2"></td> </tr> <tr> <td>i5-7300U</td> <td>2.6 GHz</td> <td>3.5 GHz</td> <td>3MB</td> </tr> </tbody> </table>	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics	Cel 3965U	2	2	2.2 GHz	-	2MB	DDR4-2133	Intel HD Graphics 610	i3-7130U	2.7 GHz	-	3MB	Intel HD Graphics 620	i5-7200U	4	4	2.5 GHz	3.1 GHz	3MB			i5-7300U	2.6 GHz	3.5 GHz	3MB	ExpressCard Smart card reader Media reader Ports	None <i>Optional:</i> Smart card reader MicroSD card reader Two USB 3.1 Gen 1 (one Always On), two USB 3.1 Type-C Gen 1, HDMI 1.4b, Ethernet (RJ-45), nano-SIM card slot (WWAN models), headphone / microphone combo jack, optional smart card reader, microSD card reader, side docking connector, security keyhole
Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics																													
Cel 3965U	2	2	2.2 GHz	-	2MB	DDR4-2133	Intel HD Graphics 610																													
i3-7130U			2.7 GHz	-	3MB		Intel HD Graphics 620																													
i5-7200U	4	4	2.5 GHz	3.1 GHz	3MB																															
i5-7300U			2.6 GHz	3.5 GHz	3MB																															
	8th Generation Intel Core i5 / i7 Processor	Monitor cable (optional)	<i>HDMI to VGA:</i> Lenovo HDMI to VGA Monitor Adapter <i>USB-C to VGA:</i> Lenovo USB-C to VGA Adapter																																	
	<table border="1"> <thead> <tr> <th>Processor Number</th> <th># of Cores</th> <th># of Threads</th> <th>Base Frequency</th> <th>Max Turbo Frequency</th> <th>Cache</th> <th>Memory Types</th> <th>Processor Graphics</th> </tr> </thead> <tbody> <tr> <td>i5-8250U</td> <td rowspan="3">4</td> <td rowspan="3">8</td> <td>1.6 GHz</td> <td>3.4 GHz</td> <td>6MB</td> <td rowspan="3">DDR4-2400</td> <td rowspan="3">Intel UHD Graphics 620</td> </tr> <tr> <td>i5-8350U</td> <td>1.7 GHz</td> <td>3.6 GHz</td> <td>6MB</td> </tr> <tr> <td>i7-8550U</td> <td>1.8 GHz</td> <td>4.0 GHz</td> <td>8MB</td> </tr> </tbody> </table>	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics	i5-8250U	4	8	1.6 GHz	3.4 GHz	6MB	DDR4-2400	Intel UHD Graphics 620	i5-8350U	1.7 GHz	3.6 GHz	6MB	i7-8550U	1.8 GHz	4.0 GHz	8MB	Camera (optional)	<i>One of the following, configurable by model:</i> • HD720p camera, fixed focus • IR camera and HD720p camera, fixed focus									
Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics																													
i5-8250U	4	8	1.6 GHz	3.4 GHz	6MB	DDR4-2400	Intel UHD Graphics 620																													
i5-8350U			1.7 GHz	3.6 GHz	6MB																															
i7-8550U			1.8 GHz	4.0 GHz	8MB																															
Graphics	Intel HD Graphics 610, 620 or Intel UHD Graphics 620 in processor only or Intel HD Graphics 620 or Intel UHD Graphics 620 in processor and AMD Radeon 530, 2GB GDDR5 memory (discrete models are NOT available in EMEA); supports external digital monitor via HDMI or USB Type-C; supports three independent displays; Max resolution: 4096x2304@60Hz (USB Type-C); 4096x2160@30Hz (HDMI)	Audio support	HD Audio, Realtek ALC3287 codec, Dolby® Audio™ / stereo speakers, 2W x 2 / dual array microphone, headphone / microphone combo jack																																	
Chipset	Intel SoC (System on Chip) platform	Keyboard UltraNav™	6-row, spill-resistant, multimedia Fn keys, numeric keypad, optional LED backlight TrackPoint™ pointing device and buttonless Mylar surface multi-touch touchpad																																	
Memory	32GB max / 2400MHz DDR4, dual-channel capable, two DDR4 SO-DIMM sockets * System clocks down for processors with lower memory controller	Security Security chip vPro (optional) Fingerprint reader	Power-on password, hard disk password, supervisor password, security keyhole Discrete TPM 2.0, TCG Certified Intel vPro Technology <i>Optional:</i> Touch style match on chip fingerprint reader on the palm rest, anti-spoofing technology																																	
Display	<i>Some:</i> 15.6" (396mm) HD (1366x768), anti-glare, LED backlight, 220 nits, 16:9 aspect ratio, 500:1 contrast ratio <i>Some:</i> 15.6" (396mm) FHD (1920x1080), anti-glare, LED backlight, IPS, 250 nits, 16:9 aspect ratio, 800:1 contrast ratio, 170° viewing angle	NFC (optional)	Near Field Communication																																	
Multi-touch	None	Battery	Integrated Li-Ion 45Wh battery, supports Rapid Charge (charge up to 80% in 1hr) with 65W USB Type-C AC adapter																																	
Storage	<i>System has one HDD slot or one M.2 2280 slot exclusively for storage</i> <i>Some:</i> HDD / SATA 6.0Gb/s, 2.5" wide, 7mm high, Active Protection System™ <i>Some:</i> SSD / SATA 6.0Gb/s, 2.5" wide, 7mm high (e.g. xxxGB SSD) <i>Some:</i> M.2 SSD / PCIe NVMe, PCIe 3.0 x 4, 32Gb/s <i>Some:</i> 128GB M.2 SSD / PCIe NVMe, PCIe 3.0 x 2, 16Gb/s, in WWAN slot as 2nd Storage, mutually exclusive with WWAN	Max battery life AC adapter	<i>MobileMark® 2014:</i> 12 hr * Battery life varies significantly with settings, usage, & other factors 45W or 65W USB Type-C AC adapter																																	
Optical	None	Preload	Windows® 10 Home 64 or Windows 10 Pro 64																																	
Ethernet	<i>Non-vPro model:</i> Intel Ethernet Connection I219-V (Jacksonville) <i>vPro model:</i> Intel Ethernet Connection I219-LM (Jacksonville)	Limited warranty	<i>One of the following, configurable by model:</i> • 1-year depot repair service • 3-year/1-yr battery depot repair service • 3-year/1-yr battery limited onsite service																																	
WLAN + Bluetooth™ (optional)	<i>One of the following, configurable by model:</i> • Realtek® RTL8822BE, Wi-Fi 2x2 802.11ac + Bluetooth 4.1, M.2 card (US only) • Intel Dual Band Wireless-AC 8265, Wi-Fi 2x2 802.11ac + Bluetooth 4.1, M.2 card * Intel 8265ac card supports BT4.2 but is limited to BT4.1 by Windows OS	Mil-Spec test	MIL-STD-810G military certification																																	
WWAN (optional)	<i>One of the following, configurable by model:</i> • Integrated Mobile Broadband 4G LTE, Intel XMM™ 7262 (Fibocom L830-EB), M.2 card (EMEA only) • Integrated Mobile Broadband 4G LTE-A, Intel XMM™ 7360 (Fibocom L850-GL), M.2 card	Environment	EPEAT™ Gold; ENERGY STAR® 6.1; RoHS-compliant																																	
SIM card (opt)	Nano-SIM card slot, optional Verizon LTE (US) SIM card																																			

ThinkPad L580

