

LightScene EV-100



DATASHEET / BROCHURE



2,000-lumen WXGA accent lighting projector in white, with a low visual noise design, ideal for retail displays, galleries and museums.

Add movement and life to your retail displays or exhibitions with a low visual noise projector that blends in beautifully to any environment, and blurs the line between lighting and projection with 2,000-lumen brightness and WXGA sharpness.

A discreet attention-grabber

The LightScene EV-100 allows you to create instantly appealing visuals with sharp WXGA resolution and 2,000-lumen brightness. Yet thanks to its low visual noise white casing, it can be used where a traditional projector would stand out, such as window displays and as part of exhibitions.

Simple, flexible implementation

A light, flexible design means the EV-100 can be installed in a variety of ways, from a traditional ceiling mount to a freestanding floor mount, or attached to an existing lighting track like a spotlight¹. It can also be mounted at and project from any angle, including portrait. The projector can be used as a traditional spotlight for when simple lighting effects are needed.

Easy to program and use

The EV-100 comes with Epson Projector Content Manager Software for quick, easy set-up without specialist installation. Playlists can easily be loaded via SD Card and changed using remote control by employees without the need for a computer. The projector can also use advanced techniques such as edge-blending to achieve stunning results in larger spaces that require multiple-unit installations.

Fit and forget reliability

A five-year, 20,000-hour warranty, coupled with Epson's durable, reliable inorganic phosphor wheel technology means that EV-100 projectors can be installed and forgotten about, and don't require regular maintenance.

KEY FEATURES

- **Discreet signage projector**
Low visual noise white casing won't grab the spotlight
- **Sharp, vivid projection**
2,000-lumen brightness and detailed WXGA resolution
- **Flexible installation**
Can be ceiling-mounted, floorstanding or attached to a lighting track
- **Easy playlist loading**
Playlist can be loaded from an SD Card without the need for a computer
- **Fit and forget reliability**
Durable Epson technology supported by a five-year 20,000-hour warranty



EPSON
EXCEED YOUR VISION

PRODUCT SPECIFICATIONS

TECHNOLOGY

Projection System	3LCD Technology
LCD Panel	0.59 inch with C2 Fine

IMAGE

Colour Light Output	2,000 lumen- 1,000 lumen (economy) In accordance with IDMS15.4
White Light Output	2,000 lumen - 1,000 lumen (economy) In accordance with ISO 21118:2012
Portrait Colour Light Output	2,000 lm
Portrait White Light Output	2,000 lm
Resolution	WXGA, 1280 x 800, 16:10
Contrast Ratio	2,500,000 : 1
Native Contrast	1,200 : 1
Keystone Correction	Manual vertical: $\pm 45^\circ$, Manual horizontal $\pm 40^\circ$
Colour Reproduction	16.77 million colours

OPTICAL

Projection Ratio	1.38 - 2.19:1
Zoom	Motorized, Factor: 1 - 1.58
Image Size	30 inches - 133 inches
Projection Distance Wide	0.9 m - 4 m
Projection Distance Tele	1.4 m - 6.3 m
Projection Distance Wide/Tele	0.88 m - 6.34 m
Projection Lens F Number	1.51 - 1.92
Focal Distance	18.2 mm - 28.4 mm
Focus	Motorized

CONNECTIVITY

Interfaces	USB 2.0 Type A, USB 2.0 Type B (Service Only), Ethernet interface (100 Base-TX / 10 Base-T), Wireless LAN b/g/n (2.4GHz), HDMI in, Stereo mini jack audio out, SD Card Slot
------------	---

ADVANCED FEATURES

Security	Wireless LAN security, Password protection
Video Colour Modes	Dynamic

LOGISTICS INFORMATION

SKU	V11H868040 V11H868041
EAN code	8715946647487
Dimensions Single Carton	535 x 477 x 244 mm
Carton Weight	9.59 Kg
Country of Origin	China



* Warranty offers are not available for all countries. Please contact your local Epson representative.

For further information please contact your local Epson office or visit www.epson-europe.com

Austria 01 253 49 78 333 Belgium +32 (0)2 792 04 47 Czech 800/142 052 Denmark 44 50 85 85 Finland 0201 552 091 France 09 74 75 04 04

(Cost of local call, operator charges may apply) Germany +49 (0) 2159/92 79 500 Greece +30 211 198 62 12 Hungary 06800 147 83 Ireland 01 436 7742

Italy 02-660321 10 (0,12 /min) Luxembourg +352 27860692 Middle East +9714 8872172 Netherlands +31 (0)20 708 5099 Norway +47 67 11 37 00

Poland 0-0-800 4911299 (0,16 zl/min) Portugal 707 222 111 Russia (095) 777-03-55 Slovakia 0850 111 429 South Africa (+2711) 465-9621

Spain 93 582 15 00 Sweden 0771-400135 (Mobilsamtal - 0,99 kr/min, Lokala samtal - 0,30 kr/min, Utlandssamtal - 0,89 kr/min) Switzerland 022 592 7923

Turkey (0212) 3360303 United Kingdom 0871 222 6702

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners. Product information is subject to change without prior notice.

LightScene EV-100

WHAT'S IN THE BOX

- User's Manual Set
- Power cable
- Remote control incl. batteries
- HDMI Cable Clamp
- Cable cover

1. Floor stand and lighting track are purchasable options.

EPSON[®]