

OpticPro A320L

plustek


OpticPro Series

Large format scanning solution
with high quality performance!



The Plustek OpticPro A320L is a high resolution, 1600 dpi scanner that can scan an A3 sized page in 7.8 seconds. Seven programmable one touch buttons simplify scanning tasks. It is ideal for graphic designers, publishing companies, libraries, schools, small office/home office (SOHO) users and for others that who cost effective require large format scanning.

❖ KEY FEATURES




• Large Format Scanning

The Plustek OpticPro A320L is designed to meet the most demanding large format scanning requirements. It features 300 dpi resolution and can scan an A3 size (297mm x 420mm , 11.7" x 16.6") color page in 7.8 seconds.



• Application

One touch buttons simplify scanning tasks and increase scanning speed and efficiency. All scanning is done using the scanner buttons. There is no need to go back and forth between your computer screen and the scanner to scan additional pages.



• Easy to Use Compatible with Most Imaging


Industry standard TWAIN and WIA drivers combined with TIFF, JPG, PDF and Microsoft Office file formats ensure compatibility with thousands of scanning and imaging programs. ABBYY FineReader is included to easily create and manage searchable PDFs.

OpticPro A320L

❖ FEATURES


Auto Mode

Automatically detects document color and scans document in color, grayscale or black & white mode.




Multi-Image Output

Scans and saves documents in 2 or 3 color modes at same time.



Color Dropout

Removes red, green or blue color when scanning forms.



Descreen Filter

Removes moiré pattern when scanning newspaper or magazine.



Hardware Requirements

Intel Core 2 Duo 2.4GHz or above
Memory: 2GB(4GB recommended)
Hard drive: 10GB Free HDD space
Interface: USB2.0 or 3.0 compatible
DVD-ROM Drive



As an international ENERGY STAR Partner, Plustek has determined that this product meets the international ENERGY STAR Program for energy efficiency.

Specification

Image Sensor	CCD
Hardware Resolution	1600 dpi
Scan Modes	Color: 48-bit input, 24-bit output Grayscale: 16-bit input, 8-bit output B/W: 1-bit output
Color Depth	Input 48-bit; Output 24-bit
Scanning Speed	7.8 sec (Color/ Grayscale/ B&W mode, 300dpi, A3)
Scanning Area (W x L)	297mm x 420mm(11.7" x 16.6"), A3
Daily Duty Scan (Sheets)	2,500
Action Button	Scan, OCR, Copy, File, Email, Custom1 & Custom2
Power Supply	24Vdc/1.25A
Power Consumption	Operation < 30W ; Idle < 3.5W ; Standby Mode < 0.5 W (Energy Star)
Interface	USB 2.0
Net Weight	7.5 Kgs (16.52 Lbs)
Dimensions (W x D x H)	623 x 400 x 133 mm (24.53" x 15.75" x 5.24")
Protocol	TWAIN Compliant
OS	Windows 7/8/10 Mac OS X 10.8 / 10.9 / 10.10 / 10.11 / 10.12
Bundled software	ABBYY FineReader12 Sprint