



# 4MP H.265 Turret IP Camera


## O4DT6M

3.3-12mm motorized lens, white housing



### Features

- Supports up to 4MP @ 30fps
- Motorized lens with auto focus
- Built-in standard PoE (IEEE 802.3af)
- H.265/H.264/MJPEG compression supported
- True Day/Night operation (IR cut filter)
- Adaptive IR LEDs reduce IR saturation
- IR Range: 98' (depending on scene reflection)
- True WDR (wide dynamic range) operation
- IP66 compliant, weather resistant
- Junction box included
- Conformance with ONVIF Profile S
- 5 year warranty



Junction Box included.



### Camera Specifications

Image Sensor	Progressive scan 1/3" CMOS, 4MP
Maximum Resolution	2592 x 1520
Minimum Illumination	F1.2, 0 lux (IR LED on)
Field of View (H)	80° - 38°
White Balance	Auto, indoor, outdoor, manual
Compensation	WDR (120dB), BLC, HLC
Day/Night	IR cut filter
Electronic Shutter Speed	1/25 - 1/100000 sec
DNR	2D/3D

### Video Specifications

Main Resolution	2592x1520 / 2560x1440 / 2304x1296 / 1980x1080 / 1280x720 @ 30fps
Compression	H.265, H.264 (HP/MP/BP), MJPEG
Bitrate Control	VBR, CBR
Multiple Streaming	3 streams

### Network Specifications

Protocols	IPv4, IPv6, TCP, UDP, RTP, RTSP, HTTP, SMTP, FTP, DHCP
DDNS Support	Speco DDNS (free of charge)
Security	User ID & password protection, IP/Mac address filtering, digest authentication
User Access	10 users max. Actual number of users may vary depending on bandwidth

### Audio Specifications

Mono Input	G.711A / G.711U
Mono Output	N/A

### Client Specifications

Web Browser Support	Windows (Internet Explorer 8 and up)
PC Application	SecureGuard® VMS
Mobile	SecureGuard® Mobile (iPhone® and Android™)

### External Terminal Specifications

Ethernet	10/100 Mbps
Power	DC jack
Analog Video Output	BNC
Microphone Input	3.5mm

### System Specifications

PoE	Standard (IEEE 802.3af)
Analytics	Motion detection, object removal, abnormality, line crossing, intrusion
Alarm Triggers	Analytics
Alarm Events	Email, FTP
Image Settings	Privacy mask, region of interest, OSD

### Operating & Unit Specifications

Power	PoE, 12VDC (power supply not included)
Power Consumption	6W
Operating Temperature	-4°F - 122°F
Operating Humidity	10% - 90% RH
Unit Dimensions	5.1" (W) x 4" (H)
Unit Weight	1.5 lbs.
Certifications	FCC, RoHS

### Optional Accessories



POEINJ  
12.95W  
PoE Injector



PSW5  
12VDC  
Power Supply

Visit [www.specotech.com](http://www.specotech.com) for latest ONVIF support. ONVIF is a trademark of Onvif, Inc. iPhone and iPad are trademarks of Apple Inc., registered in the U.S. and other countries. Android is a trademark of Google Inc. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 2/6/18

