



37-Inch Stretched Wide Screen / 16 : 4 Ratio

S37AE-OV-400G

DIGITAL SIGNAGE

GVision's commercial grade stretch wide display monitor is a unique signage monitor for customize usage. Our Super Wide monitor comes with 16 : 4 aspect ratio to display advertise or commercials for retail store such as mall, train station, subway, airport or restaurant etc.




HDMI Digital Input



VGA Analog Input



DVI Digital Input



Horz / Vert Display



700 Nit Brightness



Stretched LCD


LED

Backlight Unit



3-Year Warranty

37-Inch / Stretched WIDE DIGITAL SIGNAGE



FEATURES

- 37-Inch, 1920 x 540 Resolution
- Portrait and Landscape Supported
- Ideal for Digital Signage Display
- Video Signal: VGA (15 Pin D-Sub) / DVI / HDMI
- Customized Touch Screen is Available
- 16 : 4 WIDE Aspect Ratio
- 3-Year Warranty

SPECIFICATIONS

DISPLAY	S37AE-OV-400G
Screen Size	37"
Resolution	1920 x 540
Backlight	LED
Aspect Ratio	16 : 4
Color	16.7 M
Response Time	8ms
Brightness	700cd/m ²
Display Area (mm)	904.32 x 254.34
Contrast Ratio	4000 : 1

INTERFACE	
HDMI	1
DVI	1
VGA	1
USB	1
RS232	1
Line In	1

POWER	
Consumption	< 90W (Max)
Input Voltage	DC24V (Adapter)

TEMPERATURE	
Operating	32° F ~ 113° F (0° C ~ 45° C)
Storage	14° F ~ 140° F (-10° C ~ 60° C)

HUMIDITY	
Operating	20% ~ 80%
Storage	10% ~ 90%


DIMENSIONS (WxHxD)	
Inches (in)	36.5 x 11.1 x 2.2
Millimeter (mm)	927.7 x 281.5 x 55.8

WEIGHT	
Net Weight	21.1 lbs (9.6 kg)

VESA™	
Mount Holes (mm)	100 x 100 / 200 x 100

Specifications subject to change without any notice

INPUT INTERFACE



DIMENSION

Unit: Inch

