




Planar EP6524K

4K LCD Display

The Planar® EP6524K display offers best-in-class 24x7 reliability with the stunning image quality of 4K resolution. The Ultra HD 65" display has multi-source viewing capability, supports 4K@60Hz through both HDMI and DisplayPort, is HDCP 2.2 compliant and can be oriented in landscape or portrait. It comes fully loaded with advanced features that matter most to digital signage and other commercial applications, such as an expansion slot supporting Intel's Open Pluggable Specification (OPS) and built-in speakers. The Planar EP6524K delivers superior performance and reliability for demanding public venue, corporate and control room operations.



SPECIFICATION	DETAIL
Product Name	EP6524K
Planar Part Number	997-9252-00
Display Resolution	Ultra HD (3840 x 2160)
HD format	4K UHD 2160p
Screen Size	65 in. (diagonal)
Aspect Ratio	16:9
Display Technology	Direct-lit LED LCD
Display Active Area	56.2" x 31.6" (1428.5mm x 803.5mm)
Viewing Angle (typ)	178°
Backlight	LED
Brightness (typ)	500 nits
Response Time (typ)	8 ms ms
Frame Rate	60Hz
Contrast Ratio (typ)	4000:1
Pixel Pitch	0.372mm x 0.372mm
Color Gamut	72% NTSC
Display Color	>1 billion colors. Full 10 bit data path
External Connections	DisplayPort 1.2 x 2, HDMI 2.0 x 2 (HDCP 2.2), HDMI 1.4 x 2, VGA x 1, OPS x 1, OPS USB 2.0 x 2, OPS USB 3.0 X 1
Modes	3840x2160 @ 24/25/30/50/60Hz; 1080p @ 24/25/30/50/60Hz; 1080i @ 50/60 Hz; 480p, 576p, 720p @ 50/60 Hz
Multi-Source Views	PiP, Dual, Quad

Display Control	IR, RS-232, LAN, Keypad
Cabinet Dimensions (W x H x D)	57.7" x 33.1" x 3.4" (1465.7mm x 841.3mm x 85.5mm)
Cabinet Dimensions with Handles (W x H x D)	57.7" x 33.1" x 3.9" (1465.7mm x 841.3mm x 99.6mm)
Orientation	Landscape/Portrait
Bezel Width	0.7" (16.8mm)
Weight	86 lbs (39 kg)
Weight (Shipping)	105 lbs (48 kg)
Audio Output	PC Line Out, S/PDIF
Speakers	10W x 2 built-in
Enclosure	Metal, Industrial
Auto Brightness Control	Ambient light sensor
Mounting	VESA: 400mm x 400mm
Fanless	Yes
Line Voltage	100-240V; 50/60Hz
Power Consumption (typ)	170W (standby: <0.5W)
Operating Temperature	0° to +40°C (32° to 104°F) up to 3000m
Humidity	20 - 85% RH (non-condensing)
Options / Features	OPS slot, On/Off scheduling, Presets, TAA compliant
Approvals	FCC Class A, CE, cTUVus
Warranty	3 years Advance Exchange
Recommended Usage	Up to 24x7
In the Box	EP6524K display, power cord, HDMI cable, IR cable, remote control, and cable clamps
UPC	8 10689 00457 8

For more information, please visit www.planar.com

Specifications are subject to change without notice.

Specification Report Date: 8/20/2018

© Copyright 2018 Planar Systems, Inc. All rights reserved