



HD-TVI 2MP IR Bullet Camera with Junction Box

VLBT6W

2.8-12mm varifocal lens, white housing



Features

- Full HD resolution over coax (HD-TVI)
- Supports up to Full HD 1080p @ 30fps
- 35 built-in IR LEDs
- Signal distance up to 1600 ft.
- Full OSD operation through on-board control and UTC (up the coax)
- 12VDC operation (power supply not included)
- True WDR
- Multi-format HD (TVI, CVI, AHS, CVBS)*
- IP66 compliant, weather resistant
- 5 year warranty



Included Junction Box



Camera Specifications	
Image Sensor	1/2.8" CMOS
Maximum Resolution	1920 x 1080
Minimum Illumination	Color: 0.001lux @ F1.2
S/N Ratio	greater than 52dB
Motion Detection	Yes
Number IR LEDs	35
IR Range	98' (depending on scene reflection)
Day/Night	IR cut filter
DNR	Yes
Video Output	TVI / CVI / AHD / CVBS

Operating & Unit Specifications	
Power	12VDC (power supply not included)
Power Consumption	IR on (less than 1W) IR off (less than 4W)
Operating Temperature	-4°F - 104°F
Unit Dimensions	3.43" (Dia.) x 8.62" (L)
Unit Weight	1.3 lbs.

Optional Accessories



PSW5
12VDC
Power Supply



TVIUTPPT
HD Video
Transceiver
with Pigtail



TVIUTP
HD Video
Transceiver

* Camera is defaulted to HD-TVI. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 5/20/18