



# HD-TVI 2MP IR Turret Camera with Junction Box

## VLT7W

2.8mm fixed lens, white housing



### Features

- Full HD resolution over coax (HD-TVI)
- IR Range: 65' (depending on scene reflection)
- Supports up to Full HD 1080p @30fps
- Signal distance up to 1600 ft.
- Multi-format HD (TVI, CVI, AHD, CVBS)\*
- True WDR
- Full OSD operation through on-board control and UTC (up the coax)
- 12VDC operation (power supply not included)
- IP66 compliant, weather resistant
- 5 year warranty



Junction Box included.



Camera Specifications	
Image Sensor	1/2.8" CMOS
Maximum Resolution	1920 x 1080
Minimum Illumination	Color: 0.001lux @ F1.2
S/N Ratio	greater than 52dB
Electronic Shutter Speed	1/50 - 1/100000 sec.
Number IR LEDs	30
IR Range	65ft (depending on scene reflection)
WDR	On (Low / Middle / High) / Off
Day/Night	IR cut filter
DNR	Yes
Video Output	TVI, CVI, AHD, CVBS
Image System	PAL / NTSC

Operating & Unit Specifications	
Power	12VDC (power supply not included)
Power Consumption	IR on (less than 1W) IR off (less than 4W)
Operating Temperature	-4°F - 122°F
Unit Dimensions	4.3" (W) x 3.2" (H)
Unit Weight	1 lb.

### Optional Accessory



PSW5  
12VDC  
Power Supply



TVIUTPPT  
HD Video  
Transceiver  
with Pigtail



TVIUPT  
HD Video  
Transceiver

\* Camera defaulted to HD-TVI. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 2/7/18