



Lexmark™

CX622ade

Reliability. Security. Productivity.



CX622ade



This is a Class A device according to international electromagnetic emissions standards (i.e. FCC Rules, EN 55022/EN 55032, etc.). Class A products are intended for use in non-residential/non-domestic environments. Use of a Class A product in residential/domestic environments may cause interference to radio communications and require corrective measures.

Lexmark CX622ade

The multifunction Lexmark CX622ade combines high-impact color output as fast as 40 ppm* with single-pass, two-sided scanning that can reach 100 images per minute. In addition to reliably handling diverse media types and sizes, it comes with tools to help you minimize toner consumption and improve color accuracy.

Ready when you are

- ▶ 1.2-GHz quad-core processor and up to 6 GB memory drives printing at up to 40 ppm*.
- ▶ Scan at up to 50 pages per minute, or 100 images per minute for two-sided documents.
- ▶ Steel frame and durable design stands up to heavy use and harsh environments.
- ▶ Long-life fuser and imaging components extend uptime.
- ▶ Unison™ Toner replacement cartridges deliver up to 7000 color and 10,500 monochrome pages**.
- ▶ Keep printing in black even when color toner is empty.
- ▶ Optional hard drive offers improved system performance, enhanced scanning capabilities and additional productivity and convenience apps, including optional OCR.

Color that keeps saving

- ▶ PANTONE® calibration, embedded color sample pages and Lexmark Color Replacement produce accurate, professional color output in-house.
- ▶ Save toner with suite of tools that let you choose when and how much color to print.

Input that works

- ▶ Reliable, flexible media handling supports cardstock, small media, and envelopes from the main tray or a convenient single-sheet feeder.
- ▶ 251 pages of standard input can grow to 1451.

Interact with ease

- ▶ Tilttable 4.3-inch/10.9-cm e-Task touch screen comes with convenience and productivity apps and is customizable to meet your needs.
- ▶ Front USB port allows walk-up printing from popular file formats without a computer.
- ▶ Compact footprint allows flexible placement in more locations.
- ▶ Connect easily via Ethernet, USB, or simple mobile printing options.

Full-spectrum security

- ▶ Lexmark's full-spectrum security architecture helps keep your information safe—in the document, on the device and over the network.
- ▶ Keypoint Intelligence - Buyers Lab honored Lexmark with a prestigious BLI PaceSetter award for Document Imaging Security***.



Built for planet earth

- ▶ Energy management features reduce power consumption in active use or sleep mode.
- ▶ Standard two-sided printing saves paper.
- ▶ Recycle cartridges through the award-winning Lexmark Cartridge Collection Program (LCCP).

*Print and copy speeds measured in accordance with ISO/IEC 24734 and ISO/IEC 24735 respectively (ESAT). For more information see: www.lexmark.com/ISOspeeds.

**Average continuous black or continuous composite color (CMY) declared yield in one-sided (simplex) mode up to this number of pages in accordance with ISO/IEC 19798. Actual yield will vary considerably based upon many factors. See www.lexmark.com/yields for more information.

***Award based on North America and/or Western Europe data

Lexmark CX622ade



1 Multifunction product with 4.3-inch/10.9-cm e-Task color touch screen

18.2 x 17.4 x 23.1 inches
462 x 442 x 588 mm

2 650-sheet duo tray

5.2 x 16.7 x 16.4 inches
133 x 424 x 416 mm

3 Keyboard

1 x 11 x 5.1 inches
25 x 280 x 130 mm

4 550-sheet tray

5.2 x 16.7 x 16.4 inches
133 x 424 x 416 mm

Adjustable printer stand (not shown)

20.5 x 25.7 x 24.6 inches
521 x 653 x 625 mm

Swivel cabinet (not shown)

10.4 x 18.7 x 23.6 inches
263 x 476 x 600 mm

■ Standard

■ Optional

Note 1: Supports one optional 650-sheet duo tray; or one optional 650-sheet duo tray and one optional 550-sheet tray with the 650-sheet duo tray on top.

Note 2: All measurements are shown as height x width x depth. For more information about supported configurations, refer to the Printer, Option and Stand Compatibility Guide at http://www.lexmark.com/publications/furniture_safety/

© 2018 Lexmark. All rights reserved.

Lexmark, the Lexmark logo and Unison are trademarks of Lexmark International, Inc., registered in the United States and/or other countries. AirPrint and the AirPrint Logo are trademarks of Apple, Inc. Google Cloud Print is a trademark of Google, Inc. MOPRIA®, the Mopria® Logo™ and the Mopria® Alliance logos are trademarks, service marks, and certification marks of Mopria Alliance, Inc. in the United States and other countries. PANTONE®, PANTONE® Goe™ and other Pantone, Inc. trademarks are property of Pantone, Inc. All other trademarks are the property of their respective owners.

This product includes software developed by the OpenSSL Project for use in the Open SSL Toolkit (<http://www.openssl.org/>).

Product specifications

Lexmark CX622ade

Printing

Display	Lexmark e-Task 4.3-inch (10.9 cm) color touch screen
Print Speed: Up to ⁶	Black: 40 ppm / Color: 40 ppm
Time to First Page: As fast as	Black: <8 seconds / Color: <8 seconds
Print Resolution	Black: 1200 x 1200 dpi, 4800 Color Quality (2400 x 600 dpi) / Color: 1200 x 1200 dpi, 4800 Color Quality (2400 x 600 dpi)
Memory / Processor	Standard: 2000 MB / Maximum: 6000 MB / Quad Core, 1200 w/ GPU MHz
Hard Disk	Option available
Recommended Monthly Page Volume ²	1500 - 10000 pages
Maximum Monthly Duty Cycle: Up to ³	100000 pages per month

Copying

Copy Speed: Up to ⁶	Black: 40 cpm / Color: 40 cpm
Time to First Copy: As fast as	Black: 8 seconds / Color: 8.5 seconds

Scanning

Scanner Type / ADF Scan	Flatbed scanner with ADF / DADF (single pass Duplex)
A4/Ltr Duplex Scan Speed: Up to	Black: 94 / 100 sides per minute / Color: 60 / 64 sides per minute
A4/Ltr Simplex Scan Speed: Up to	Black: 47 / 50 sides per minute / Color: 30 / 32 sides per minute
ADF Paper Input Capacity: Up to	100 pages 20 lb or 75 gsm bond

Faxing

Modem Speed	Max is 33,600 bps, V.34 Half-Duplex Kbps
-------------	--

Supplies⁷

Laser Cartridge Yields (up to) ¹	1,400-page Colour (CMY) Cartridges, 2,000-page Black Cartridge, 5,000-page Colour (CMY) Extra High Yield Cartridges, 8,500-page Black Extra High Yield Cartridge, 7,000-page Colour (CMY) Ultra High Yield Cartridges, 10,500-page Black Ultra High Yield Cartridge
Photoconductor Estimated Yield: Up to ⁵	125,000 pages, based on 3 average letter/A4-size pages per print job and ~ 5% coverage
Cartridge(s) Shipping with Product ¹	2,000-page color (CMY) Return Program Toner Cartridges, 3,000-page Black Starter Return Program Toner Cartridge

Paper Handling

Included Paper Handling	250-Sheet Input, 150-Sheet Output Bin, Integrated Duplex, Single-Sheet Manual Feed
Optional Paper Handling	550-Sheet Tray, 650-Sheet Duo Tray
Paper Input Capacity: Up to	Standard: 250+1 pages 20 lb or 75 gsm bond / Maximum: 1450+1 pages 20 lb or 75 gsm bond
Paper Output Capacity: Up to	Standard: 150 pages 20 lb or 75 gsm bond / Maximum: 150 pages 20 lb or 75 gsm bond
Media Types Supported	Card Stock, Paper Labels, Plain Paper, Vinyl Labels, Refer to the Card Stock & Label Guide.
Media Sizes Supported	10 Envelope, 7 3/4 Envelope, 9 Envelope, A4, A5, B5 Envelope, C5 Envelope, DL Envelope, Hagaki Card, Executive, Folio, JIS-B5, Legal, Letter, Statement, Universal, Oficio, A6

General Information⁴

Standard Ports	USB 2.0 Specification Hi-Speed Certified (Type B), Gigabit Ethernet (10/100/1000), Front USB 2.0 Specification Hi-Speed Certified port (Type A), Rear USB 2.0 Specification Hi-Speed Certified Port (Type A)
Optional Network Ports	Marknet N8372 WiFi Option
Noise Level: Operating	Print: 52 dBA / Copy: 55 dBA / Scan: 51 dBA
Specified Operating Environment	Humidity: 8 to 80% Relative Humidity, Temperature: 10 to 32°C (50 to 90°F), Altitude: 0 - 2896 Meters (9,500 Feet)
Limited Warranty - See Statement of Limited Warranty	1-Year Onsite Service, Next Business Day
Size (in. - H x W x D) / Weight (lb.)	18.2 x 17.4 x 23.1 in. / 60 lb.

All information in this brochure is subject to change without notice. Lexmark is not liable for any errors or omissions.

This is a Class A device according to international electromagnetic emissions standards (i.e. FCC Rules, EN 55022/EN 55032, etc.).

Class A products are intended for use in non-residential/non-domestic environments. Use of a Class A product in residential/domestic environments may cause interference to radio communications and require corrective measures.

¹Average continuous black or continuous composite CMY declared cartridge yield up to this number of standard pages in accordance with ISO/IEC 19798. ²Recommended Monthly Page Volume" is a range of pages that helps customers evaluate Lexmark's product offerings based on the average number of pages customers plan to print on the device each month. Lexmark recommends that the number of pages per month be within the stated range for optimum device performance, based on factors including: supplies replacement intervals, paper loading intervals, speed, and typical customer usage. ³Maximum Monthly Duty Cycle" is defined as the maximum number of pages a device could deliver in a month using a multishift operation. This metric provides a comparison of robustness in relation to other Lexmark printers and MFPs. ⁴Printers are sold subject to certain license/agreement conditions. See www.lexmark.com/printerlicense for details. ⁵Actual Yield may vary based on other factors such as device speed, paper size and feed orientation, toner coverage, tray source, percentage of black-only printing and average print job complexity. ⁶Print and copy speeds measured in accordance with ISO/IEC 24734 and ISO/IEC 24735 respectively (ESAT). For more information see: www.lexmark.com/ISOspeeds. ⁷Product functions only with replacement cartridges designed for use in a specific geographical region. See www.lexmark.com/regions for more details.