

## OVERVIEW

Basic rPDUs deliver reliable power to critical IT equipment within a rack or cabinet.

### Benefits

- Reliable rack power distribution.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.
- Standard three-year warranty, upgraded to a five-year warranty with product registration.



## Part #: VP7541

**Model Number:** XPB240-103IJ4TL6

**Category:** Basic

**Sub Category:** Standard

**Power Configuration:** 30A, 208V, 4.9kW

**Physical Configuration:** 66in / 1683mm, Vertical


**Product Summary:** VP7541 - rPDU, Basic Standard, 30A, 208V, 4.9kW, Vertical, (20) IEC C13, (4) IEC C19, 10ft power cord with L6-30P, Black Powder Coat.

### Plug Form:



L6-30P

### Receptacle:



IEC C13  
(Quantity: 20)



IEC C19  
(Quantity: 4)

### Chassis Color Options:



To discuss color options, contact your local sales representative.

## Product Specification and Options

### System Features

|                              |       |
|------------------------------|-------|
| Quantity Of Inputs           | 1     |
| Voltage                      | 208V  |
| Current                      | 30A   |
| VA per Input (Load Capacity) | 4.9kW |

|  |   |
|--|---|
| <b>Frequency</b>   | 50/60Hz   |
| <b>Over Current Protection</b>                               | (2) 20A Double Pole Magnetic Breakers   |
| <b>Switch</b>  | Breaker/Switch Combination  |
| <b>Power Cable Wire Gauge</b>                                | 10/3  |
| <b>Power Cable Length</b>                                    | 10ft  |
| <b>Plug Type</b>   | NEMA L6-30P Twistlock   |
| <b>Combined Total Receptacle/Socket Quantity</b>             | 24  |
| <b>Receptacle/Socket Type #1</b>                             | IEC C13   |
| - Quantity on Face   | 20  |
| - Quantity per Breaker                                       | 10  |
| - Style  | Banks of 5  |
| - Maximum Output per Receptacle/Socket                       | 15A per receptacle bank   |
| - Voltage per Receptacle/Socket                              | 208V  |
| <b>Receptacle/Socket Type #2</b>                             | IEC C19   |
| - Quantity on Face   | 4   |
| - Quantity per Breaker                                       | 2   |
| - Style  | Individual  |
| - Maximum Output per Receptacle/Socket                       | 20A   |
| - Voltage per Receptacle/Socket                              | 208V  |
| <b>Continuous Operating Temperature Range</b>                | 10-45C / 50-113F  |
| <b>Heavy Steel - Powder Coat Finish</b>                      | Black   |
| <b>Configuration</b>   | 66in / 1683mm Vertical Rackmount  |
| <b>7938 Vertical Mounting Bracket Kit</b>                    | Yes   |
| <b>Toolless Mounting Hardware - Center to Center Spacing</b> | 61.25in and 64.75in   |
| <b>Made in the USA</b>                                       | Yes, TAA Compliant  |
| <b>Product Warranty</b>                                      | 5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years |
| <b>Certification/Agency Approvals</b>                        | RoHS Compliant  |
| <b>Certification/Agency Approvals</b>                        | UL & c-UL Listed 60950  |
| <b>Chassis Dimensions (LxWxD)</b>                            | 66.25in x 2.0in x 2.0in   |
| <b>Doghouse (D)</b>  | 1.44in  |
| <b>Shipped Weight</b>  | 17lbs (7.71kg)  |