

ThinkCentre M715 Tiny Thin Client (2nd Gen) 10VL0005US

Product

ThinkCentre M715 Tiny Thin Client (2nd Gen)

Region

NA

Country/Region

USA

Machine Type

10VL

TopSeller

TopSeller

Processor

AMD PRO A10-8770E (4C / 4T, 2.8 / 3.5 GHz, 2MB L2)

Chipset

AMD B300 Chipset

Graphics

Integrated AMD Radeon R7 Graphics

Memory

1x 4GB DDR4-2666

Storage

1x 32GB SSD M.2 2242 SATA

Optical

None

Speaker

1.5Wx1

Ethernet

Integrated 100/1000M

WLAN + Bluetooth

QCA6174A 11ac, 2x2 + BT4.2

Optional Rear Ports

1x Serial

Chassis Intrusion Switch

Chassis Intrusion Switch

Kensington Cable Lock

None

Adapter Cage

None

Toolless Chassis Screw

None

Dust Filter

None

VESA Mount

None

Color

Black

Stand

Stand

Keyboard

USB Traditional Keyboard, Black, English

Mouse

USB Calliope Mouse

Power Supply

65W 88% Adapter

Additional Certificates

None

Monitor Cable

None

System Management

DASH

Operating System

LeTOS V2, English

Bundled Software

None

Base Warranty

3-year, Onsite

Bundled Service

None

EAN / UPC / JAN

192563938088

End of Support

2025-01-19

Announce Date

2018-11-15

Recommended Services**Best**

4Y Lenovo Protect (Premier Support + Keep Your Drive + Accidental Damage Protection) (5PS0N73191)

Better

4Y Lenovo Support (Premier Support + Keep Your Drive) (5PS0N73243)

Good

3Y Premier Support Upgrade from 3Y Onsite (5WS0U26647)

Notes:**California Electronic Waste Recycling Fee**

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

L WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



ThinkCentre M715 Tiny Thin Client (2nd Gen) Platform Specifications

Product Specifications Reference (PSREF)



Processor	AMD Athlon, A6, A10, or Ryzen processor						Keyboard <i>Some:</i> Lenovo Calliope Keyboard (USB connector), black <i>Some:</i> Lenovo Traditional Keyboard (USB connector), black <i>Some:</i> Lenovo Calliope Wireless Keyboard (2.4GHz via USB receiver), black <i>Some:</i> Lenovo Calliope Mouse (USB connector), black <i>Some:</i> Lenovo Fingerprint Mouse (USB connector), Windows Hello support, black <i>Some:</i> Lenovo Calliope Wireless Mouse (2.4GHz via USB receiver), black	
	APU		Cores / Threads	Frequency Base/Max	L2 / L3 Cache	Memory Sup-port (Up to)		Integrated Graphics
	Athlon PRO 200GE		2 / 4	3.2 GHz	1 MB / 4MB	DDR4-2666		Radeon Vega 3
	PRO A6-8570E		2 / 2	3.0 / 3.4 GHz	1 MB / -	DDR4-2400		Radeon R5
	PRO A10-8770E		4 / 4	2.8 / 3.5 GHz	2 MB / -	DDR4-2400		Radeon R7
Ryzen 3 PRO 2200GE		4 / 4	3.2 / 3.6 GHz	2 MB / 4MB	DDR4-2933	Radeon Vega 8		
Memory	8GB max, DDR4 2666*, two 260-pin SO-DIMM sockets, dual-channel capable * System automatically clocks down for the lower memory controller						Mechanical Tiny (1L), black color; metal case ● Toolless chassis open (need optional toolless chassis screw) ● Optional dust filter	
Disk	<i>Some:</i> 32GB M.2 Solid State Drive (SSD) / SATA interface <i>Some:</i> 128GB M.2 Solid State Drive (SSD) / PCIe NVMe, PCIe 3.0 x 2							
Optical	None						VESA mount Optional VESA mount bracket kit, supports VESA 75mm and 100mm Floor Stand Optional system floor stand for vertical orientation	
Onboard SATA	One SATA cable (1-drop to device), one SATA 6.0Gb/s connector on planar							
Graphics	AMD Radeon™ Graphics in processor, uses main memory, DirectX® 12, two DisplayPort™, one optional port (HDMI, VGA, or 3rd DP), supports 3 independent displays (supports maximum of 2 concurrent HDMI/DVI displays when using HDMI port or DP to DVI/HDMI dongles, and Athlon / Athlon PRO only support 2 displays); <i>Max resolution:</i> 4096x2160 (DP) @60Hz; 4096x2160 (HDMI) @30Hz; 1920x1200 (VGA) @60Hz						Power supply 65 watts AC/DC adapter, autosensing, 88% PSU (not included for TIO models)	
Monitor cable	Optional DP to VGA dongle, DP to DVI-D dongle, or DP to HDMI 1.4 dongle							
Chipset	AMD B300 Chipset						Limited warranty 1-year or 3-year, limited onsite service / service upgrades available	
Front ports* (Std.)	Two USB 3.1 Gen1 (one is Always On and fast charge), one microphone (stereo, 3.5mm), one headphone / microphone combo jack (stereo, 3.5mm)						Preload Preloaded operating system <i>Some:</i> Windows Embedded Standard 7 V2 (WES 7 V2) <i>Some:</i> Windows 10 IoT Enterprise <i>Some:</i> LeTOS V2 (Lenovo Terminal Operating System, Linux-based)	
Rear ports* (Std.)	One USB 3.1 Gen1 and three USB 2.0, ethernet (RJ-45), two DisplayPort, one headphoneone							
Rear ports* (Opt.)	One optional port (VGA**, 3rd DP**, HDMI**, or serial on some models) * Depending on many factors, actual data transfer speed may be lower than theoretical speed ** Not support VGA, 3rd DP, HDMI for the models with Athlon / Athlon PRO						Environment ENERGY STAR® 7.0*, EPEAT™ Silver rating* (*not for non-OS models); ErP Lot 3; RoHS-compliant	
Audio support	High Definition (HD) Audio, Realtek ALC233-VB2 / internal speaker (1.5 watt)						MIL-SPEC test MIL-STD-810G military certification (Low Pressure [Altitude], High Temperature, Low Temperature, Temperature Shock, Humidity, Sand and Dust, Vibration, Shock)	
WLAN	<i>Some:</i> 11ac wireless, M.2 Card, Realtek RTL8821CE (dual band), Wi-Fi + Bluetooth 4.2* combo adapter, 1x1 <i>Some:</i> 11ac wireless, M.2 Card, Qualcomm Atheros QCA9377 (dual band), Wi-Fi + Bluetooth 4.2* combo adapter, 1x1 <i>Some:</i> 11ac wireless, M.2 Card, Realtek RTL8822BE (dual band), Wi-Fi + Bluetooth 4.2* combo adapter, 2x2 <i>Some:</i> 11ac wireless, M.2 Card, Qualcomm Atheros QCA6174A (dual band), Wi-Fi + Bluetooth 4.2* combo adapter, 2x2 <i>Some:</i> Bluetooth 4.2* wireless, integrated in Wi-Fi + BT combo adapter						Accessories For compatible accessories, please go to http://smartfind.lenovo.com	
Bluetooth	* Hardware supports BT 4.2, but Win10 RS3 and earlier only supports BT 4.1							
Ethernet	Gigabit ethernet, Realtek RTL8111EPV, Wake on LAN®							
Manageability	DASH 1.0/1.1							
Security chip	Discrete TPM 2.0, TCG Certified							
Security features	<ul style="list-style-type: none"> ● Security slot (in rear for optional Kensington® MicroSaver® cable) ● Padlock loop ● Smart USB protection, allows keyboard/ mouse only, blocks all storage devices ● Power-on password ● Administrator password ● Hard disk password ● Boot sequence control ● Boot without keyboard and mouse ● Individual USB port disablement ● Chassis intrusion switch 							

Note: The specifications above may not be available in all regions.

Lenovo, April 2020

ThinkCentre M715 Tiny Thin Client (2nd Gen)

