



22E1H

21.5 inch (54.68 cm) LCD MONITOR

21.5-inch viewable; Full HD ergonomic business display

General	
Model name	22E1H
Product Line	Essential-line
Series	E1
Channel	B2B
Classification	Mainstream
Section	Business
Launch date	01-06-2018

Screen	
Resolution	1920x1080
Refresh rate	60Hz
Screen size (inch)	21.5 inch
Screen size (cm)	54.68 cm
Flat / Curved	Flat
Backlight	WLED
Panel Type	TN
Aspect ratio	16:9
Display Colours	16.7 Million
Panel Colour in Bits	8
sRGB Coverage (%)	99
Adobe RGB Coverage (%)	73
Active Screen Area (WxH) (mm)	476.64 x 268.1 mm
Pixel Pitch	0.24825
Scanning Frequency	"30 -83kHz (H) 50 -76 Hz (V)"
Response time (GtG)	2 ms
Contrast (static)	1000:1
Contrast (dynamic)	20M:1
Brightness (typical)	250 cd/m²
Viewing angle (CR10)	170/160 °
Hard Glass	3H
OSD languages	EN, FR , ES, PT, DE, IT, NL, SE, FI, PL ,CZ, RU, KR, CN (T), CN (S), JP

Exterior	
Monitor colour	Black
Bezel Type	Normal
Removable Stand	✓

Ergonomics	
Vesa Wallmount	100x100
Tilt	-3.5° ~ 21.5 °

Multimedia		
Audio output	Headphone out (3.5mm)	
Connectivity and Multimedia		
Signal Input	HDMI 1.4 x 1, VGA	
What's in the Box?		
VGA cable (m)	1.8 m	
Power Cable C13	1.8 m	
Power / Environmental		
Powersupply	Internal	
Powersource	100 - 240V 50/60Hz	
PowerConsumption On (Energystar)	18 watt	
PowerConsumption Standby (Energystar)	0.5 watt	
EnergyClass	A	
Approbations / Regulations		
TCO	7	
EPEAT	Yes	
Listed on Epeat Website	✓	
Rohs compliant	✓	
Warranty		
Pixel Policy	ISO 9241-307	
Warranty Period	3 Years	
MTBF	50.000 hours	
Dimensions / Weights		
Product height (mm)	393	
Product width (mm)	504	
Product depth (mm)	199.4	
Product Dimensions (incl base) (in)	19.85 x 15.5 x 7.85 inch	
Carton Dimensions	564x 401x137 mm	
Product Dimensions (incl base) (mm)	504.4x393.7x199.4 mm	
Gross Weight (incl package) (kg)	3.8 Kg	
Net Weight (excl package) (kg)	2.64 Kg	
Texts and USP		
Marketing title	21.5 inch 1920x1080@60Hz 2 ms TN HDMI 1.4 x 1, VGA	

Features

Flicker-free

