# iMouse W4 Waterproof Antimicrobial Optical Mouse

www.adesso.com



## Waterproof Design

The Adesso iMouse W4 has a waterproof design that's rated for IP66. Its waterproof design housing protects its internal electrical parts and provides proctection from powerful water jets, oil, and dust.

### Antimicrobial

Made with antimicrobial materials, this device prevents the growth of harmful bacteria and protects against the build up germs between washings.

## Enhanced Optical Sensor

Optical sensor technology improves precision and even lets you work on most surfaces such as wood, marble and leather without a need of mouse pad.

### 1000 DPI Resolution

The iMouse W4 provides responsive, smooth cursor control, precise tracking and easy text selection thanks to its high-definition optical tracking (1000 DPI).



Design

#### Specifications:

Tracking Method: **DPI** Resolution: Buttons: Switch Lifecycle: Hand Orientation: Dimensions: Weight: Cable Length:

**Optical Sensor** 1,000 DPI 3 Buttons (Right, Left Click, Middle Button) 3 Million Right 4.7" x 2.5" x 1.5" (119 x 64 x 37 mm) 0.2 lb. (95 g) 6 ft. (1.8 m)

#### **Requirements:**

**Operating System** 

Connectivity Interface

Windows® 7 & above Mac<sup>®</sup> OS X 10.6 USB port

Includes:

Adesso iMouse W4

#### **Shipping Information:**

ltem	UPC Code	Package Dimensions	Package Weight	Qty/Carton
iMouse W4	783750009355	7.25" X 5.3" x 3.00"	0.3 lb.	10/40
iMouse W4W	783750009362	7.25" X 5.3" x 3.00"	0.3 lb.	10/40



