



WPL206 | Light-Duty Desktop Label Printer **No-Nonsense Barcode Printer with Perfect Balance Between Price and Performance**



Key Features

- High quality double-walled clamshell design
- 5 inches per second print speed
- 64 MB SDRAM and 128 MB Flash memory
- Easy media loading
- USB 2.0 standard
- WPL firmware for plug-n-play ease
- ENERGY STAR® qualified

WPL206 | Light-Duty Desktop Label Printer

RESOLUTION	203 DPI (8 dots/mm)
PRINTING METHOD	Direct Thermal
PRINT SPECS	Max Print Speed: 5 IPS (127 mm per second) Max Print Width: 4.25 in (108 mm) Max Print Length: 90 in (2,286 mm) Max Label Capacity: 5 in OD (127 mm)
PHYSICAL SPECS	Dimensions: 6.77 in (W) x 6.50 in (H) x 7.68 in (D) / 172 mm (W) x 165 mm (H) x 195 mm (D) Weight: 2.87 lbs. (1.3 kg)
PROCESSOR & MEMORY	32-bit RISC CPU; 128 MB Flash memory, 64 MB SDRAM
INTERFACE	USB 2.0
POWER	External universal switching power supply Input: AC 100-240V, 50-60Hz Output: DC 24V, 2.5A, 60W
OPERATION	1 power switch, 1 feed button & 1 LED (3 colors: green, amber & red)
SENSORS	Transmissive gap sensor, Black mark reflective sensor, Head open sensor
INTERNAL FONTS	8 alpha-numeric bitmap fonts, Monotype Imaging® true type font engine with one CG Triumvirate Bold Condensed scalable font
BARCODE	1D Barcode: Code 39, Code 93, Code128UCC, Code128 subsets A,B,C, Codabar, Interleave 2 of 5, EAN-8, EAN-13, EAN-128, UPC-A, UPC-E, EAN and UPC 2(5) digits add-on, MSI, PLESSEY, POSTNET, RSS-Stacked, GS1 DataBar, Code 11, China Post; 2D Barcode: PDF-417, Maxicode, DataMatrix, QR code, Aztec, MicroPDF417
FONT & BARCODE ROTATION	0, 90, 180, 270 degree
PRINTER LANGUAGE	WPL (Compatible to EPL, ZPL, ZPL II)
MEDIA TYPE	Continuous, black mark, fan-fold, notched (outside wound)
MEDIA SPECS	Width: 0.7 in ~ 4.5 in (19 mm ~ 114 mm) Thickness: 2.16 ~ 7.48 mil (0.055 mm ~ 0.19 mm) Core Diameter: 1 in ~ 1.5 in (25.4 mm ~ 38 mm) Label Length: 0.39 in ~ 90 in (10 mm ~ 2,286 mm)
ENVIRONMENT	Operation: 41 ~ 104°F, 25 ~ 85% non-condensing Storage: -40 ~ 140°F, 10 ~ 90% non-condensing
SAFETY	FCC Class A, CE Class A, C-Tick Class A, CB, CCC, ENERGY STAR®
ENVIRONMENTAL CONCERN	Comply with RoHS, WEEE
INCLUDED	Windows labeling software CD disk, Quick start guide, USB cable, Power cord
WARRANTY	2 Year Limited
ACCESSORIES	WPL206 Peel-off module, WPL206 Guillotine cutter - full cut or partial cut programmable, WPL206 Print head, 203DPI, KP-200 Plus keyboard display unit

