

Not for use in European Markets

Hospital-Grade Power Cord, NEMA 5-15P to Locking IEC C13 - Green Dot, 10A, 125V, 18 AWG, 3 ft. (0.91 m), Black

MODEL NUMBER: P006-L03-HG10



Connects a PC, printer, monitor, scanner or other hospital equipment with a C14 inlet to a grounded hospital-grade AC outlet.

Features

Hospital-Grade Power Cable is a Safe Solution for Medical Facilities This hospital-grade IEC power cord is designed for computers, mobile carts, printers, scanners, monitors and other compatible equipment with a three-pin C14 inlet in a hospital or other medical facility. It features a locking C13 end for connecting to a device and a NEMA 5-15P-HG plug for connecting to a hospital-grade AC power source located outside patient-care vicinities. The three-foot length allows you flexibility in placing equipment with respect to the power outlet.

Locking C13 Connector Helps Prevent Accidental Disconnection and Expensive Downtime Having a cable come loose accidentally can mean the loss of power and costly downtime. The locking C13 connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

Lifetime Warranty The P006-L03-HG10 is backed by a lifetime warranty, ensuring reliability and performance.

Highlights

- Recommended for connecting devices to power outlets outside patient care vicinities
- 3-ft. (0.91 m) length allows flexibility in placing devices, while avoiding cable clutter
- Hospital-grade power cable replaces or upgrades power cord provided by manufacturer
- NEMA 5-15P-HG plug connects to AC power; C13 plug connects to device's C14 inlet
- Locking C13 connector maintains secure link to avoid loss of power and costly downtime

Applications

- Connect a mobile cart battery, monitor, computer or printer to a hospital-grade surge protector up to 3 ft. away in a hospital environment outside patient care vicinities
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P006-L03-HG10 Hospital-Grade Power Cord, NEMA 5-15P to Locking IEC C13, 3 ft., Black

Specifications

OVERVIEW	
UPC Code	037332223142



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Device Compatibility	Mobile Cart; Computer; Printer; Monitor/HDTV; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
PHYSICAL	
Color	Black
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
Cable Length (ft.)	3
Cable Length (m)	0.9
Cable Length (in.)	36
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	25.40 x 18.01 x 1.27
Shipping Dimensions (hwd / in.)	10.00 x 7.09 x 0.50
Shipping Weight (kg)	0.17
Shipping Weight (lbs.)	0.37
ENVIRONMENTAL	
Operating Temperature Range	-4 to 221 F (-20 to 105 C)
Storage Temperature Range	-4 to 221 F (-20 to 105 C)
Relative Humidity	0-65% RH
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P-HG
Side B - Connector 1	IEC-320-C13 - LOCKING
SPECIAL FEATURES	
High Voltage	No
Locking Plug	Yes
STANDARDS & COMPLIANCE	
Certifications	ANSI/UL 62 and 817, CAN/CSA C22.2 NO. 21 and 49, RoHS, REACH
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>