

USB C Multiport Video Adapter w/ HDMI, VGA, Mini DisplayPort or DVI - USB Type C Monitor Adapter to HDMI 2.0 or mDP 1.2 (4K 60Hz) - VGA or DVI (1080p) - Space Gray Aluminum

Product ID: CDPVDHMDMP2G



This USB-C™ multiport video adapter offers a portable solution for connecting your USB Type-C laptop to a VGA, DVI, HDMI® or Mini DisplayPort (mDP) display.

All-in-One Video Connectivity with Travel in Mind

Avoid the hassle of carrying different adapters, with a 4-in-1 USB-C monitor adapter. With VGA, DVI, HDMI and mDP output, you can connect your laptop to any display using this multiport adapter.

The adapter features a magnetic retainer that guides the breakout cable into place for quick, secure portability. With a durable aluminum enclosure, the adapter can withstand being carried in your travel bag.



Ultra HD 4K 60Hz Resolution

The HDMI and mDP outputs on this USB-C video adapter support UHD resolutions up to 4K 60Hz, while the VGA and DVI outputs support HD resolutions up to 1920 x 1200.

Stylish Connectivity for Your MacBook, MacBook Pro, or Any Laptop

The USB-C adapter has a Space Gray housing and built-in USB-C cable designed to match your Space Gray MacBook, or MacBook Pro. The adapter is compatible with USB-C DP Alt Mode devices.

The adapter is also available with 4K 30Hz HDMI resolution support, in three colors: Space Gray (CDPVDHMDPSG), Rose Gold (CDPVDHMDPRG) and Silver (CDPVGDVHMDMP), so you can choose an adapter that matches your laptop or your color preference.

CDPVDHMDMP2G is backed by a StarTech.com 3-year warranty and free lifetime technical support.



Certifications, Reports and Compatibility



Applications

- Connect to virtually any display while traveling
- Connect your MacBook to a provided VGA, DVI, HDMI or mDP display at work or school
- Connect a secondary VGA, DVI, HDMI or mDP monitor to your Space Gray MacBook

Features

- 4-IN-1 MULTIPORT USB-C VIDEO ADAPTER: USB-C DP Alt Mode to any one of HDMI 2.0 (4K 60Hz & 7.1ch audio), mDP 1.2 (4K 60Hz & 2ch audio), VGA or DVI (1080p), HDCP 2.2/1.4, Thunderbolt 3 compatible
- TOUGH & PORTABLE: Durable aluminum space gray enclosure with a magnetically-secured hideaway cable wrap for on-the-go users in the office, at home, boardrooms, and classrooms
- COMPATIBILITY: USB-C display adapter for Dell XPS/Precision/Latitude, Lenovo ThinkPad X1 Carbon/Extreme, Surface Laptop 3/Surface Book 3, TB3 MacBook Pro/Air, HP EliteBook/Spectre/ZBook, Chromebooks
- TESTED & VERIFIED: USB Type-C adapter tested @ 4K 60Hz mini DisplayPort/HDMI or 1080p VGA/DVI for compatibility w/ TV, monitor & projector brands like Dell, Asus, Acer, LG, Samsung, Sharp, Sony, Epson
- EASY TO USE: Supporting a driverless plug-and-play setup, this adapter is fully compatible with multiple OS platforms: Windows / macOS / Linux / Chrome OS

Hardware	Warranty	3 Years	
	Active or Passive Adapter	Active	
	Adapter Style	Adapters	
	AV Input	USB-C	
	AV Output	HDMI - 1.4 Mini DisplayPort - 1.2 DVI-I (Digital Only) - Single-Link VGA	
	Chipset ID	Cypress - CYPD3120 Parade - PS8348 Parade - PS8617 Parade - PS8338 Parade - PS171 Parade - PS176	
	Performance	Audio Specifications	HDMI - 7.1 Channel Audio DVI - No Audio Support VGA - No Audio Support Mini DisplayPort - 5.1 Channel Audio
Maximum Analog Resolutions		1920 x 1200 @ 60Hz	
Maximum Cable Distance To Display		49.9 ft [15.2 m]	
Maximum Digital Resolutions		4096 X 2160 @ 24Hz or 3840 X 2160 @ 60Hz (HDMI) 4096 X 2160 @ 60Hz (mDP)	
MTBF		800,703 hours	
Supported Resolutions		Maximum HDMI output: 4096 X 2160 @ 24Hz or 3840 X 2160 @ 60Hz Maximum mDP output: 4096 X 2160 @ 60Hz Maximum DVI and VGA output: 1920 x 1200 @ 60Hz <i>Lower resolutions and refresh rates may also be supported</i>	
Video Revision		HDMI 2.0 DisplayPort 1.2	
Wide Screen Supported		Yes	
Connector(s)		Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode Male Input
		Connector B	1 - Mini-DisplayPort (20 pin) Female Output

1 - VGA (15 pin, High Density D-Sub) Female Output
1 - DVI-I (29 pin) Female Output
1 - HDMI (19 pin) Female Output

Special Notes / Requirements	Note	<p>Only one video output is supported on the video adapter at a time, if multiple connections are made, only one of the outputs will function</p> <p>Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling</p>
Environmental	Humidity	<p>Storage: 5% ~ 90 % RH (no condensation) Operating: 10% ~ 85 % RH (no condensation)</p>
	Operating Temperature	0°C to 45°C (32°F to 113°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
Physical Characteristics	Cable Length	4.5 in [115 mm]
	Color	Space Gray
	Material	Aluminum
	Product Height	1.2 in [3 cm]
	Product Length	6.9 in [17.5 cm]
	Product Width	5.6 in [14.2 cm]
	Weight of Product	6.5 oz [185 g]
Packaging Information	Package Height	0.6 in [16 mm]
	Package Length	2.2 in [55 mm]
	Package Width	4.1 in [10.5 cm]
	Shipping (Package) Weight	0.3 lb [0.1 kg]
What's in the Box	Included in Package	1 - travel A/V adapter

Product appearance and specifications are subject to change without notice.