

# 24MK600M-B.AUS

24" 3-Side Borderless IPS FHD Monitor

**24" FHD (1920 x 1080) IPS Display**

**3-Side Borderless Design**

**Radeon FreeSync™ Technology**

**Dual HDMI**

**On Screen Control**



## PICTURE QUALITY

Screen Size	24" Flat
Panel Type	IPS 3-Side Borderless
Color Gamut (CIE1931)	NTSC 72%
Color Depth(Number of Colors)	16.7M colors
Pixel Pitch(mm)	0.2745 x 0.2745
Response Time (GTG)	5ms (Faster)
Refresh Rate	75Hz
Aspect Ratio	16:9
Resolution	1920 x 1080
Brightness	250cd/m <sup>2</sup> (Typ.) 200cd/m <sup>2</sup> (Min.)
Contrast Ratio	1000:1 (Typ.) Mega
Viewing Angle	178/178
Surface Treatment	Anti glare, 3H

## INPUT/OUTPUT

HDMI	Yes x 2
D-Sub	Yes
Headphone Out	Yes
<b>POWER</b>	
Type	Adapter
Input	100-240V (50/60Hz)
Output	19V/1.3A
Normal On (EPA Typ.)	14.1W
Normal On (factory out condition Typ.)	17.5W
Power Save/Sleep Mode (Max)	Under 0.3W
DC Off (Max)	Under 0.3W

## SPECIAL FEATURES

Picture Mode	Custom, Reader, Color Weakness, Photo, Cinema, Game
Ratio	Wide/Original
DDC/CI	Yes
HDCP	Yes (Ver 1.4)
Plug & Play	Yes
Response Time Control	Yes
Color Calibrated	Yes
Adaptive Sync	Radeon FreeSync™
DAS Mode	Yes
Black Stabilizer	Yes
Crosshair	Yes
Automatic Standby	Yes
Smart Energy Saving	Yes
Super Resolution +	Yes
On Screen Control (OSC)	Yes
Black Level	Yes
DFC	Yes
Gamma Control	Yes
Color Temperature	Yes
R/G/B Color Control	Yes
OSD Lock	Yes
Auto Adjustment(D-sub Only)	Yes
<b>DIMENSIONS/WEIGHT</b>	
With Stand (WxHxD)	21.2" x 16.4" x 7.2"
Without Stand (WxHxD)	21.2" x 12.7" x 2.6"
Shipping Dimensions (WxHxD)	24.1" x 15.4" x 5.5"
With Stand Weight	6.8 lbs
Without Stand Weight	6.1 lbs
Shipping Weight	9.5 lbs

## STAND

Base Detachable	Yes
Tilt(Angle)	-2-15 Degree

## CABINET / ACCESSORIES

Wall Mount Size (mm)	75 x 75
Power Cord	Option
HDMI	Yes
S/W Install CD	Yes
Easy Setup Guide	Yes
Manual	Yes

## STANDARD

UL(cUL)	Yes
TUV-Type	Yes
FCC-B, CE	Yes
CCC (for China)	Yes
KC	Yes
VCCI	Yes
EPA 7.0	Yes
ErP	Yes
EPEAT(USA)	Yes
Windows 10	Yes

## LIMITED WARRANTY / UPC

Limited Warranty	1 Year Parts and Labor
UPC	719192622487
Country of Origin	China