

ThinkVision X1 (2nd GEN) MONITOR

EXTREME STYLISH, EXTREME FOREFRONT.



Lenovo™

THE MILESTONE OF X-SERIES, 27" FULL-SCREEN, 4K, THUNDERBOLT™ 3 MONITOR.

Pushing the limit of screen share ratio with innovative technology, the 27" Lenovo™ ThinkVision® X1 (2nd GEN) display brings full-screen and ultra-slim appearance in elegant design. With 4K resolution and >99% sRGB color gamut, you will be assured of excellent watching experience and Thunderbolt™ 3 interface will bring the best user experience. "Motor" camera is first used on monitor, which will move up and down automatically and with it you will own standard VoIP system.

WHY YOU SHOULD BUY THE LENOVO THINKVISION X1 (2nd GEN) MONITOR



Full-screen appearance

With world's slimmest (4.7 mm) 27" 4K TBT monitor you will experience full-screen 4-side borderless display with the screen ratio of approximately 93%. The monitor also comes with a metal stand and a base.



Brilliant performance

The 4K UHD IPS screen displays 3840 x 2160 resolution at 60 Hz, 99% sRGB color gamut, 10-bit depth, with 1.07 billion color support assures you stunning visuals and superb color experience.



Convenient user experience

Total versatility with Thunderbolt™ 3 interface supporting 4K + USB 3.0 & 45 PD motor-camera with dual-array microphone. The monitor's metal stand comes attached with a Think RedBot tracking button.

THE LENOVO THINKVISION X1 (2nd GEN) MONITOR IS BEST SUITED FOR



The Executives and CXO of company.



SOHO and Gold Collars with high income.



Trendsetters who pursue an extreme and forefront monitor.



ThinkVision X1 (2nd GEN) MONITOR



SPECIFICATIONS

DISPLAY		ENVIRONMENTAL	
Panel Size	27"	Temperature	
Panel Type	In-Plane Switching	Operating	0°C - 45°C
Backlight	WLED	Non-Operating	-20°C - 60°C
Resolution	3840 (H) x 2160 (V)	Humidity	
Aspect Ratio	16:9	Operating	8% - 80%
Anti-Glare	Yes	Non-Operating	5% - 95%
Screen Dimensions (W x H) (mm)	596.7 (H) x 335.7 (V)	Altitude	
Maximum Brightness (Typical)	350 cd/m ²	Operating	16,000 ft
Viewing Angle (H/V at CR 10:1)	178°/178°	Non-Operating	40,000 ft
Contrast Ratio (Typical)	1000:1	Arsenic-Free Glass	Yes
Dynamic Contrast Ratio	3M:1	PVC-Free	N/A
Pixel Pitch (W x H) (mm)	0.1554 x 0.1554	Mercury-Free	Yes
Dot/Pixel Per Inch (DP/PPi)	163	PCC % of Plastic Resins	25%
Color Gamut (CIE 1931)	99% sRGB		
Response Time (Extreme/Typical/Off)	4/6/14 ms (G-to-G)		
POWER CONSUMPTION		DIMENSIONS (W x D x H)	
Typical	65 W	Size Packed	
Maximum	135 W	(mm)	718 x 140 x 470
Sleep-Mode	0.5 W	(inches)	28.27" x 5.51" x 18.5"
Switch Off-Mode	0.5 W	Size Unpacked with Stand	
Power Supply	External	Lowest Position	
Power Voltage	90 VAC - 264 VAC	(mm)	609.74 x 234.81 x 123.05
Voltage Dynamic Frequency	47 Hz - 63 Hz	(inches)	24" x 9.24" x 4.84"
SIGNAL INPUT		Highest Position	
Video Input Signals	DisplayPort™ 1.2 + HDMI™ 2.0 + Thunderbolt™ 3	(mm)	609.74 x 234.81 x 474.76
Video Cables Supplied	HDMI™ + USB Type-C™	(inches)	24" x 9.24" x 18.69"
Video Cable Length	1.8 m	Size Unpacked without Stand	
USB Hub	Yes (4 x USB 3.0)	(Monitor Head Only)	
USB Cable Supplied	USB Type-A to C	(mm)	609.74 x 32.7 x 351.71
Audio-Out	Yes (3.5 mm)	(inches)	24" x 1.29" x 13.85"
SIGNAL INTERFACE / PERFORMANCE		Distance from Table to Panel	
Horizontal Frequency	30 kHz - 60 kHz	Lowest Pixel at Bottom of Screen	
Vertical Frequency	23 Hz - 80 Hz	(mm / inches)	9.55 / 0.376"
Native Resolution	3840 x 2160	Highest Pixel at Top of Screen	
Maximum Pixel Clock Speed/ Bandwidth	20 Gbps	(mm / inches)	6.5 / 0.256"
Default Color Temperature	6500K	Stand Base Footprint Area	
Preset Modes	24	(mm)	234.66 x 234.66
OSD Buttons	2 Buttons + Tracking Point	(inches)	9.24" x 9.24"
OSD Languages	English, French, Italian, German, Spanish, Japanese, Chinese, Russian	Weight	
		Packed	Starting at < > lbs (< > kg)
		Unpacked	Starting at 12.32 lbs (5.59 kg)
		Monitor Head Only	Starting at 9.46 lbs (4.29 kg)
MECHANICAL		COMPLIANCE	
Tilt Angle (Front / Back)	-5° / 30°	EPEAT™	Silver
Swivel Angle (Left / Right)	N/A	ENERGY STAR® Rating	7.0
Lift (mm)	N/A	ULE	Silver
Pivot	N/A	TCO®	7.0
VESA® Mount (mm)	N/A	RoHS (EU 2002/95/EC)	Yes
Kensington® Lock Slot	Yes	Windows Certification	Windows 7 / Windows 10
Cable Management	Yes	China Energy Efficiency Standard	Tier 2
Bezel Color	N/A		
Bezel Width			
Top (mm / inches)	N/A		
Bottom (mm / inches)	1.85 / 0.07"		
Sides (mm / inches)	N/A		
WARRANTY AND AVAILABILITY		Warranty	
		3 Years	
		Geography Availability	WW



WWW.LENOVO.COM

Lenovo reserves the right to alter product offerings and specifications at any time, without notice. Lenovo makes every effort to ensure accuracy of all information but is not liable or responsible for any editorial, photographic or typographic errors. All images are for illustration purposes only. For full Lenovo product, service and warranty specifications visit www.lenovo.com. Lenovo makes no representations or warranties regarding third party products or services. **Trademarks:** The following are trademarks or registered trademarks of Lenovo: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkServer, ThinkVantage and ThinkVision. Microsoft, Windows and Vista are registered trademarks of Microsoft Corporation. Ultrabook, Celeron, Celeron Inside, Core Inside, Intel, Intel Logo, Intel Atom, Intel Atom Inside, Intel Core, Intel Inside, Intel Inside Logo, Intel vPro, Itanium, Itanium Inside, Pentium, Pentium Inside, vPro Inside, Xeon, Xeon Phi, and Xeon Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product and service names may be trademarks or service marks of others. Battery life (and recharge times) will vary based on many factors including system settings and usage. Visit www.lenovo.com/lenovo/us/en/safecom/ periodically for the latest information on safe and effective computing. ©2017 Lenovo. All rights reserved.

Lenovo