

I10003L

Model Number: MN01X4W1-36PT68-3TL6A0A10-S
Category: Basic
Sub Category: Upgradeable
Power Configuration: 30A, 208V, 4.9kW
Physical Configuration: 72in / 1829mm, Vertical



Description: I10003L provides reliable power distribution where you need it in the rack. With the Geist Upgradeable hot-swap technology, users may easily transform basic PDUs to metered or monitored PDUs with the addition of the appropriate Interchangeable Monitoring Device (IMD) module; all without causing any interruption.

Product Summary: I10003L - Basic, Upgradeable, 30A, 208V, Vertical, (30) Locking IEC C13, (6) Locking IEC C19, breakered, 10 ft power cord with L6-30P, No Monitoring (Upgradeable with IMD module). Black Powder Coat.


Monitoring: No Monitoring (Upgradeable with IMD module)

Plug Form:



L6-30P

Receptacle:



Locking IEC C13
(Quantity: 30)



Locking IEC C19
(Quantity: 6)

Chassis Colors Options:



To discuss color options, contact your local sales representative.

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Product Specification and Options:

Monitoring	No Monitoring (Upgradeable with IMD module)
Quantity Of Inputs	1
Voltage	208V
Current	30A
VA per Input (Load Capacity)	4.9kW
Frequency	50/60Hz
Over Current Protection	(2) 20A Double Pole Magnetic Breakers
Switch	Breaker/Switch Combination
Power Cable Wire Gauge	10/3
Power Cable Length	10ft
Power Entry Location	Bottom Front
Plug Type	NEMA L6-30P Twistlock
Combined Total Receptacle/Socket Quantity	36
Receptacle/Socket Type #1	U-Lock IEC C13
- Quantity on Face	30
- Quantity per Breaker	15
- U-Lock Color ID	2 Circuit = Orange, Green
- Style	Individual
- Voltage per Receptacle/Socket	208V
Receptacle/Socket Type #2	U-Lock IEC C19
- Quantity on Face	6
- Quantity per Breaker	3
- U-Lock Color ID	2 Circuit = Orange, Green
- Style	Individual
- Voltage per Receptacle/Socket	208V
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	72in / 1829mm Vertical Rackmount
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Chassis Dimensions (LxWxD)	72in x 2in x 2in
Shipped Weight	16lbs (7.26kg)

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com