

12659

Model Number: XPB308-103IN6TL15
Category: Basic
Sub Category: Standard
Power Configuration: 30A, 208V DELTA, 8.6kW
Physical Configuration: 66in / 1683mm, Vertical



Description: The 12659 functions as a basic power strip without built-in surge protection. This unit is ideal for installations in facilities with proper surge protection at the main electrical service entrance.

Product Summary: 12659 - Basic, Standard, 30A, 208V DELTA, 3 Phase, Vertical, (24) IEC C13, (6) IEC C19, breakered, 10 ft power cord with L15-30P, Black Powder Coat.

Plug Form:



L15-30P

Receptacle:



IEC C13
(Quantity: 24)



IEC C19
(Quantity: 6)

Chassis Colors Options:



To discuss color options, contact your local sales representative.

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Product Specification and Options:

Quantity Of Inputs	1
Voltage	208V Delta
Current	30A x 3 Phase DELTA
VA per Input (Load Capacity)	8.6kW
Frequency	50/60Hz
Over Current Protection	(3) 20A Double Pole Magnetic Breakers
Switch	Breaker/Switch Combination
Power Cable Wire Gauge	10/4
Power Cable Length	10ft
Plug Type	NEMA L15-30P Twistlock
Combined Total Receptacle/Socket Quantity	30
Receptacle/Socket Type #1	IEC C13
- Quantity on Face	24
- Quantity per Breaker and Phase Combination	8
- Style	Banks of 4
- Maximum Output per Receptacle/Socket	15A per receptacle bank
- Voltage per Receptacle/Socket	208V
Receptacle/Socket Type #2	IEC C19
- Quantity on Face	6
- Quantity per Breaker and Phase Combination	2
- Style	Individual
- Maximum Output per Receptacle/Socket	20A
- Voltage per Receptacle/Socket	208V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	66in / 1683mm Vertical Rackmount
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	66.25in x 2.0in x 2.0in
Doghouse (D)	1.44in
Shipped Weight	17lbs (7.71kg)

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com