

## 28131

**Model Number:** NSVAN100-102S20TL  
**Category:** Basic  
**Sub Category:** Standard  
**Power Configuration:** 20A, 120V, 1.9kW  
**Physical Configuration:** 39in / 978mm, Vertical



**Description:** The 28131 functions as a basic power strip without built-in surge protection. This unit is ideal for installations in facilities with proper surge protection at the main electrical service entrance.

**Product Summary:** 28131 - Basic, Standard, 20A, 120V, Vertical, (10) NEMA 5-20R, breakered, 10 ft power cord with L5-20P, Black Powder Coat.

**Plug Form:**



L5-20P

**Receptacle:**



NEMA 5-20R  
(Quantity: 10)

**Chassis Colors Options:**



*To discuss color options, contact your local sales representative.*

**Geist Americas**

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

**Geist Europe**

+44 (0) 1823.275100  
geistglobal.com

**Geist Asia**

China  
+86.755.86639505  
geistglobal.com

## Product Specification and Options:

Quantity Of Inputs	1
Voltage	120V
Current	20A
VA per Input (Load Capacity)	1.9kW
Frequency	50/60Hz
Over Current Protection	20A Thermal Breaker
Switch	No
Indicators - LED(s)	1 - Power ON Green LED
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA L5-20P Twistlock
Receptacle/Socket Type #1	NEMA 5-20R
- Quantity on Face	10
- Quantity per Breaker	10
- Style	Individual - In-Line
- Maximum Output per Receptacle/Socket	20A
- Voltage per Receptacle/Socket	120V
Center to Center Receptacle Spacing	2.95
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	39in / 978mm Vertical Rackmount
Plastic Mounting Clips	1 - Bottom; 1 - Top
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	38.50in x 1.61in x 1.61in
Shipped Weight	6lbs (2.72kg)