

38584

Model Number: NSVBC200-102R20
Category: Metered
Sub Category: Standard
Power Configuration: 20A, 120V, 1.9kW
Physical Configuration: 66in / 1683mm, Vertical



Description: The 38584 is a PDU equipped with a local power meter displaying real-time power metrics. This metered PDU is ideal for installations in facilities with proper surge protection at the main electrical service entrance.

Product Summary: 38584 - Metered, Standard, 20A, 120V, Vertical, (20) NEMA 5-20R, power switch, breakered, 10 ft power cord with 5-20P, Power - Local (A, V, W, PF)
Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input. Black Powder Coat.

Monitoring: Power - Local (A, V, W, PF)
Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input

Plug Form:



5-20P

Receptacle:



NEMA 5-20R
(Quantity: 20)

Chassis Colors Options:



To discuss color options, contact your local sales representative.

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Product Specification and Options:

| | |
|--|---|
| Monitoring | Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input |
| Monitoring Level 1 | Aggregate - Total Unit Monitoring |
| Quantity Of Inputs | 1 |
| Voltage | 120V |
| Current | 20A |
| VA per Input (Load Capacity) | 1.9kW |
| Frequency | 50/60Hz |
| Over Current Protection | 20A Thermal Breaker |
| Switch | Yes |
| Indicators - LED(s) | 1 - Power ON Green LED |
| Power Cable Wire Gauge | 12/3 |
| Power Cable Length | 10ft |
| Plug Type | NEMA 5-20P |
| Receptacle/Socket Type #1 | NEMA 5-20R |
| - Quantity on Face | 20 |
| - Style | Individual - Rotated |
| - Maximum Output per Receptacle/Socket | 20A |
| - Voltage per Receptacle/Socket | 120V |
| Center to Center Receptacle Spacing | 2.8 |
| Continuous Operating Temperature Range | 10-45C / 50-113F |
| Heavy Steel - Powder Coat Finish | Black |
| Configuration | 66in / 1683mm Vertical Rackmount |
| Plastic Mounting Clips | 1 - Bottom; 2 - Top |
| Made in the USA | Yes |
| Product Warranty | 5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years |
| Certification/Agency Approvals | RoHS Compliant |
| Certification/Agency Approvals | UL & c-UL Listed 60950 |
| Chassis Dimensions (LxWxD) | 66.25in x 1.61in x 1.61in |
| Shipped Weight | 9lbs (4.08kg) |

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com