

## 12193

**Model Number:** VHV BAN242-102C13TL6  
**Category:** Metered  
**Sub Category:** Standard  
**Power Configuration:** 20A, 208V, 3.3kW  
**Physical Configuration:** 66in / 1683mm, Vertical



**Description:** The 12193 is a PDU equipped with a local power meter displaying real-time power metrics. This metered PDU is ideal for installations in facilities with proper surge protection at the main electrical service entrance.

**Product Summary:** 12193 - Metered, Standard, 20A, 208V, Vertical, (24) IEC C13, 10 ft power cord with L6-20P, Current - Local  
 Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input. Black Powder Coat.


**Monitoring:** Current - Local  
 Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input

**Plug Form:**



L6-20P

**Receptacle:**



IEC C13  
(Quantity: 24)

**Chassis Colors Options:**



*To discuss color options, contact your local sales representative.*

**Geist Americas**

800.432.3219  
 geistglobal.com

Geist DCIM  
 1.877.449.4150  
 geistglobal.com

**Geist Europe**

+44 (0) 1823.275100  
 geistglobal.com

**Geist Asia**

China  
 +86.755.86639505  
 geistglobal.com

## Product Specification and Options:

Monitoring	Current - Local Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Monitoring Level 1	Aggregate - Total Unit Monitoring
Quantity Of Inputs	1
Voltage	208V
Current	20A
VA per Input (Load Capacity)	3.3kW
Frequency	50/60Hz
Over Current Protection	None
Switch	No
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA L6-20P Twistlock
Receptacle/Socket Type #1	IEC C13
- Quantity on Face	24
- Style	Banks of 4
- Maximum Output per Receptacle/Socket	15A per receptacle bank
- Voltage per Receptacle/Socket	208V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	66in / 1683mm Vertical Rackmount
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	66.25in x 1.72in x 1.61in
Shipped Weight	13lbs (5.9kg)

### Geist Americas

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

### Geist Europe

+44 (0) 1823.275100  
geistglobal.com

### Geist Asia

China  
+86.755.86639505  
geistglobal.com