


## I10136L

**Model Number:** MN01X5W1-42PZ63-3TL56A0A10-S-A  
**Category:** Basic  
**Sub Category:** Upgradeable  
**Power Configuration:** 30A, 230/400V WYE, 16.6kW  
**Physical Configuration:** 75in / 1905mm, Vertical



**Description:** I10136L provides reliable power distribution where you need it in the rack. With the Geist Upgradeable hot-swap technology, users may easily transform basic PDUs to metered or monitored PDUs with the addition of the appropriate Interchangeable Monitoring Device (IMD) module; all without causing any interruption.

**Product Summary:** I10136L - Basic, Upgradeable, 30A, 230/400V WYE, 3 Phase, Vertical, (36) Locking IEC C13, (6) Locking IEC C19, Alternating Phase/Circuits, breakered, 10 ft power cord with L22-30P, No Monitoring (Upgradeable with IMD module). Black Powder Coat.


**Monitoring:** No Monitoring (Upgradeable with IMD module)

**Plug Form:**



L22-30P

**Receptacle:**



Locking IEC C13  
(Quantity: 36)



Locking IEC C19  
(Quantity: 6)

**Chassis Colors Options:**



*To discuss color options, contact your local sales representative.*

**Geist Americas**

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

**Geist Europe**

+44 (0) 1823.275100  
geistglobal.com

**Geist Asia**

China  
+86.755.86639505  
geistglobal.com

## Product Specification and Options:

Monitoring	No Monitoring (Upgradeable with IMD module)
Quantity Of Inputs	1
Voltage	230/400V WYE
Current	30A x 3 Phase WYE
VA per Input (Load Capacity)	16.6kW
Frequency	50/60Hz
Over Current Protection	(6) 20A Single Pole Magnetic Breakers
Switch	Breaker/Switch Combination
Power Cable Wire Gauge	10/5
Power Cable Length	10ft
Power Entry Location	Bottom Front
Plug Type	NEMA L22-30P Twistlock
Combined Total Receptacle/Socket Quantity	42
Alternating Phase/Circuits	Yes
Receptacle/Socket Type #1	U-Lock IEC C13
- Quantity on Face	36
- Quantity per Breaker	6
- Quantity per Phase	12
- U-Lock Color ID	6 Circuit = Orange, Green, Blue, Light Orange, Light Green, Light Blue
- Style	Individual
- Voltage per Receptacle/Socket	230V
Receptacle/Socket Type #2	U-Lock IEC C19
- Quantity on Face	6
- Quantity per Breaker	1
- Quantity per Phase	2
- U-Lock Color ID	6 Circuit = Orange, Green, Blue, Light Orange, Light Green, Light Blue
- Style	Individual
- Voltage per Receptacle/Socket	230V
Center to Center Receptacle Spacing	1U
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	75in / 1905mm Vertical Rackmount
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Made in the USA	Yes

Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	75in x 3.5in x 2in
Shipped Weight	19lbs (8.62kg)

#### Geist Americas

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

#### Geist Europe

+44 (0) 1823.275100  
geistglobal.com

#### Geist Asia

China  
+86.755.86639505  
geistglobal.com