



I10133L

Model Number: MN01X5W1-42PZ68-3TL15A0A10-S-A
Category: Basic
Sub Category: Upgradeable
Power Configuration: 30A, 208V DELTA, 8.6kW
Physical Configuration: 75in / 1905mm, Vertical



Description: I10133L provides reliable power distribution where you need it in the rack. With the Geist Upgradeable hot-swap technology, users may easily transform basic PDUs to metered or monitored PDUs with the addition of the appropriate Interchangeable Monitoring Device (IMD) module; all without causing any interruption.

Product Summary: I10133L - Basic, Upgradeable, 30A, 208V DELTA, 3 Phase, Vertical, (36) Locking IEC C13, (6) Locking IEC C19, Alternating Phase/Circuits, breakered, 10 ft power cord with L15-30P, No Monitoring (Upgradeable with IMD module). Black Powder Coat.

Monitoring: No Monitoring (Upgradeable with IMD module)

Plug Form:



L15-30P

Receptacle:



Locking IEC C13
(Quantity: 36)



Locking IEC C19
(Quantity: 6)

Chassis Colors Options:



To discuss color options, contact your local sales representative.

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Product Specification and Options:

Monitoring	No Monitoring (Upgradeable with IMD module)
Quantity Of Inputs	1
Voltage	208V Delta
Current	30A x 3 Phase DELTA
VA per Input (Load Capacity)	8.6kW
Frequency	50/60Hz
Over Current Protection	(3) 20A Double Pole Magnetic Breakers
Switch	Breaker/Switch Combination
Power Cable Wire Gauge	10/4
Power Cable Length	10ft
Power Entry Location	Bottom Front
Plug Type	NEMA L15-30P Twistlock
Combined Total Receptacle/Socket Quantity	42
Alternating Phase/Circuits	Yes
Receptacle/Socket Type #1	U-Lock IEC C13
- Quantity on Face	36
- Quantity per Breaker and Phase Combination	12
- U-Lock Color ID	3 Circuit = Orange, Green, Blue
- Style	Individual
- Voltage per Receptacle/Socket	208V
Receptacle/Socket Type #2	U-Lock IEC C19
- Quantity on Face	6
- Quantity per Breaker and Phase Combination	2
- U-Lock Color ID	3 Circuit = Orange, Green, Blue
- Style	Individual
- Voltage per Receptacle/Socket	208V
Center to Center Receptacle Spacing	1U
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	75in / 1905mm Vertical Rackmount
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	FCC Part 15 Class A Conformance

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	75in x 3.5in x 2in
Shipped Weight	19lbs (8.62kg)

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com