

## 12656

**Model Number:** XPB248-103D20TL15  
**Category:** Basic  
**Sub Category:** Standard  
**Power Configuration:** 30A, 208V DELTA, 8.6kW  
**Physical Configuration:** 66in / 1683mm, Vertical



**Description:** The 12656 functions as a basic power strip without built-in surge protection. This unit is ideal for installations in facilities with proper surge protection at the main electrical service entrance.

**Product Summary:** 12656 - Basic, Standard, 30A, 208V DELTA, 3 Phase, Vertical, (24) NEMA 6-20R, breakered, 10 ft power cord with L15-30P, Black Powder Coat.

**Plug Form:**



L15-30P

**Receptacle:**



NEMA 6-20R  
(Quantity: 24)

**Chassis Colors Options:**



*To discuss color options, contact your local sales representative.*

## Product Specification and Options:

Quantity Of Inputs	1
Voltage	208V Delta
Current	30A x 3 Phase DELTA
VA per Input (Load Capacity)	8.6kW
Frequency	50/60Hz
Over Current Protection	(3) 20A Double Pole Magnetic Breakers
Switch	Breaker/Switch Combination
Power Cable Wire Gauge	10/4
Power Cable Length	10ft
Plug Type	NEMA L15-30P Twistlock
Receptacle/Socket Type #1	NEMA 6-20R
- Quantity on Face	24
- Quantity per Breaker and Phase Combination	8
- Style	Duplex
- Maximum Output per Receptacle/Socket	20A
- Voltage per Receptacle/Socket	208V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	66in / 1683mm Vertical Rackmount
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	66.25in x 2.0in x 2.0in
Doghouse (D)	1.44in
Shipped Weight	17lbs (7.71kg)