

I10131L

Model Number: MN01X4W1-30PN63-3PS56B0A10-S-A
Category: Basic
Sub Category: Upgradeable
Power Configuration: 30A, 230/400V WYE, 16.6kW
Physical Configuration: 72in / 1829mm, Vertical



Description: I10131L provides reliable power distribution where you need it in the rack. With the Geist Upgradeable hot-swap technology, users may easily transform basic PDUs to metered or monitored PDUs with the addition of the appropriate Interchangeable Monitoring Device (IMD) module; all without causing any interruption.

Product Summary: I10131L - Basic, Upgradeable, 30A, 230/400V WYE, 3 Phase, Vertical, (24) Locking IEC C13, (6) Locking IEC C19, Alternating Phase/Circuits, breakered, 10 ft power cord with 3P+N+E (IP44), No Monitoring (Upgradeable with IMD module). Black Powder Coat.

Monitoring: No Monitoring (Upgradeable with IMD module)

Plug Form:



3P+N+E (IP44)

Receptacle:



Locking IEC C13
(Quantity: 24)



Locking IEC C19
(Quantity: 6)

Chassis Colors Options:



To discuss color options, contact your local sales representative.

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Product Specification and Options:

| | |
|---|---|
| Monitoring | No Monitoring (Upgradeable with IMD module) |
| Quantity Of Inputs | 1 |
| Voltage | 230/400V WYE |
| Current | 30A x 3 Phase WYE |
| VA per Input (Load Capacity) | 16.6kW |
| Frequency | 50/60Hz |
| Over Current Protection | (6) 20A Single Pole Magnetic Breakers |
| Switch | Breaker/Switch Combination |
| Power Cable Wire Gauge | 10/5 |
| Power Cable Length | 10ft |
| Power Entry Location | Bottom Front |
| Plug Type | IEC60309 3P + N + E, 30A, Splashproof IP44 |
| Combined Total Receptacle/Socket Quantity | 30 |
| Alternating Phase/Circuits | Yes |
| Receptacle/Socket Type #1 | U-Lock IEC C13 |
| - Quantity on Face | 24 |
| - Quantity per Breaker | 4 |
| - Quantity per Phase | 8 |
| - U-Lock Color ID | 6 Circuit = Orange, Green, Blue, Light Orange, Light Green, Light Blue |
| - Style | Individual |
| - Voltage per Receptacle/Socket | 230V |
| Receptacle/Socket Type #2 | U-Lock IEC C19 |
| - Quantity on Face | 6 |
| - Quantity per Breaker | 1 |
| - Quantity per Phase | 2 |
| - U-Lock Color ID | 6 Circuit = Orange, Green, Blue, Light Orange, Light Green, Light Blue |
| - Style | Individual |
| - Voltage per Receptacle/Socket | 230V |
| Maximum Operating Temperature | 60C / 140F |
| Heavy Steel - Powder Coat Finish | Black |
| Configuration | 72in / 1829mm Vertical Rackmount |
| 7938 Vertical Mounting Bracket Kit | Yes |
| Toolless Mounting Hardware - Center to Center Spacing | 61.25in and 64.75in |
| Made in the USA | Yes |
| Product Warranty | 5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years |

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

| | |
|--------------------------------|---------------------------------|
| Certification/Agency Approvals | FCC Part 15 Class A Conformance |
| Certification/Agency Approvals | RoHS Compliant |
| Certification/Agency Approvals | UL & c-UL Listed 60950 |
| Chassis Dimensions (LxWxD) | 72in x 2in x 2.25in |
| Shipped Weight | 17lbs (7.71kg) |

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com