

16824

Model Number: NSVBAN200-101S15
Category: Metered
Sub Category: Standard
Power Configuration: 15A, 120V, 1.4kW
Physical Configuration: 66in / 1683mm, Vertical



Description: The 16824 is a PDU equipped with a local power meter displaying real-time power metrics. This metered PDU is ideal for installations in facilities with proper surge protection at the main electrical service entrance.

Product Summary: 16824 - Metered, Standard, 15A, 120V, Vertical, (20) NEMA 5-15R, breakered, 10 ft power cord with 5-15P, Current - Local

Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input. Black Powder Coat.

Monitoring: Current - Local

Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input

Plug Form:



5-15P

Receptacle:



NEMA 5-15R
(Quantity: 20)

Chassis Colors Options:



To discuss color options, contact your local sales representative.

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Product Specification and Options:

Monitoring	Current - Local Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Monitoring Level 1	Aggregate - Total Unit Monitoring
Quantity Of Inputs	1
Voltage	120V
Current	15A
VA per Input (Load Capacity)	1.4kW
Frequency	50/60Hz
Over Current Protection	15A Thermal Breaker
Switch	No
Indicators - LED(s)	1 - Power ON Green LED
Power Cable Wire Gauge	14/3
Power Cable Length	10ft
Plug Type	NEMA 5-15P
Receptacle/Socket Type #1	NEMA 5-15R
- Quantity on Face	20
- Quantity per Breaker	20
- Style	Individual - In-Line
- Maximum Output per Receptacle/Socket	15A
- Voltage per Receptacle/Socket	120V
Center to Center Receptacle Spacing	2.8
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	66in / 1683mm Vertical Rackmount
Plastic Mounting Clips	1 - Bottom; 2 - Top
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	66.25in x 1.61in x 1.61in
Shipped Weight	9lbs (4.08kg)