

39133

Model Number: NSVKN080-102S20
Category: Basic
Sub Category: Standard
Power Configuration: 20A, 120V, 1.9kW
Physical Configuration: 24in / 610mm, Vertical



Description: The 39133 functions as a basic power strip without built-in surge protection. This unit is ideal for installations in facilities with proper surge protection at the main electrical service entrance.

Product Summary: 39133 - Basic, Standard, 20A, 120V, Vertical, (8) NEMA 5-20R, breakerless, 10 ft power cord with 5-20P, Black Powder Coat.

Plug Form:



5-20P

Receptacle:



NEMA 5-20R
(Quantity: 8)

Chassis Colors Options:



To discuss color options, contact your local sales representative.

Product Specification and Options:

Quantity Of Inputs	1
Voltage	120V
Current	20A
VA per Input (Load Capacity)	1.9kW
Frequency	50/60Hz
Over Current Protection	20A Thermal Breaker
Switch	No
Indicators - LED(s)	1 - Power ON Green LED
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA 5-20P
Receptacle/Socket Type #1	NEMA 5-20R
- Quantity on Face	8
- Quantity per Breaker	8
- Style	Individual - In-Line
- Maximum Output per Receptacle/Socket	20A
- Voltage per Receptacle/Socket	120V
Center to Center Receptacle Spacing	2.0
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	24in / 600mm Vertical Rackmount
Plastic Mounting Clips	1 - Bottom; 1 - Top
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	24.00in x 1.61in x 1.61in
Shipped Weight	5lbs (2.27kg)

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com