

38653

Model Number: NSVL080-101S15
Category: Basic
Sub Category: Standard
Power Configuration: 15A, 120V, 1.4kW
Physical Configuration: 17in / 432mm, Horizontal/Vertical



Description: The 38653 functions as a basic power strip without built-in surge protection. This unit is ideal for installations in facilities with proper surge protection at the main electrical service entrance.

Product Summary: 38653 - Basic, Standard, 15A, 120V, Horizontal/Vertical, (8) NEMA 5-15R, power switch, breakered, 10 ft power cord with 5-15P, Black Powder Coat.

Plug Form:



5-15P

Receptacle:



NEMA 5-15R
(Quantity: 8)

Chassis Colors Options:



To discuss color options, contact your local sales representative.

Product Specification and Options:

| | |
|--|---|
| Quantity Of Inputs | 1 |
| Voltage | 120V |
| Current | 15A |
| VA per Input (Load Capacity) | 1.4kW |
| Frequency | 50/60Hz |
| Over Current Protection | 15A Thermal Breaker |
| Switch | Yes |
| Indicators - LED(s) | 1 - Power ON Green LED |
| Power Cable Wire Gauge | 14/3 |
| Power Cable Length | 10ft |
| Plug Type | NEMA 5-15P |
| Receptacle/Socket Type #1 | NEMA 5-15R |
| - Quantity on Face | 8 |
| - Quantity per Breaker | 8 |
| - Style | Individual - In-Line |
| - Maximum Output per Receptacle/Socket | 15A |
| - Voltage per Receptacle/Socket | 120V |
| Center to Center Receptacle Spacing | 1.25 |
| Continuous Operating Temperature Range | 10-45C / 50-113F |
| Heavy Steel - Powder Coat Finish | Black |
| Configuration | 17in / 432mm Vertical/Horizontal Rackmount |
| 19in Panel Mount Brackets | Yes |
| Plastic Mounting Clips | 1 - Bottom; 1 - Top |
| Made in the USA | Yes |
| Product Warranty | 5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years |
| Certification/Agency Approvals | RoHS Compliant |
| Certification/Agency Approvals | UL & c-UL Listed 60950 |
| Chassis Dimensions (LxWxD) | 17.00in x 1.61in x 1.61in |
| Shipped Weight | 4lbs (1.81kg) |

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com