

## 17380

**Model Number:** VSSBAN204-101S15  
**Category:** Metered  
**Sub Category:** Surge  
**Power Configuration:** 15A, 120V, 1.4kW  
**Physical Configuration:** 66in / 1683mm, Vertical



**Description:** 17380 is a surge-protected PDU equipped with a local power meter displaying real-time power metrics. This metered PDU is ideal for environments lacking facility-level surge suppression or for applications requiring additional protection.

**Product Summary:** 17380 - Metered, Surge, 15A, 120V, Vertical, (20) NEMA 5-15R, breakered, 10 ft power cord with 5-15P, Current - Local  
Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input. Black Powder Coat.

**Monitoring:** Current - Local  
Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input

**Plug Form:**



5-15P

**Receptacle:**



NEMA 5-15R  
(Quantity: 20)

**Chassis Colors Options:**



*To discuss color options, contact your local sales representative.*

**Geist Americas**

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

**Geist Europe**

+44 (0) 1823.275100  
geistglobal.com

**Geist Asia**

China  
+86.755.86639505  
geistglobal.com

## Product Specification and Options:

Monitoring	Current - Local Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Monitoring Level 1	Aggregate - Total Unit Monitoring
Quantity Of Inputs	1
Voltage	120V
Current	15A
VA per Input (Load Capacity)	1.4kW
Frequency	50/60Hz
Over Current Protection	15A Thermal Breaker
Switch	No
Indicators - LED(s)	1 - Power ON Green LED
Power Cable Wire Gauge	14/3
Power Cable Length	10ft
Plug Type	NEMA 5-15P
Receptacle/Socket Type #1	NEMA 5-15R
- Quantity on Face	20
- Quantity per Breaker	20
- Style	Individual - In-Line
- Maximum Output per Receptacle/Socket	15A
- Voltage per Receptacle/Socket	120V
Center to Center Receptacle Spacing	2.8
Joule Rating	720
Maximum Clamping Voltage	340V
Response Time	< 5 nanoseconds
Technology Used	Super MOVs
Surge Indicator Red LED	Yes
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	66in / 1683mm Vertical Rackmount
Plastic Mounting Clips	1 - Bottom; 2 - Top
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Connected Equipment Warranty	5 years / \$5,000
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	66.25in x 1.61in x 1.61in

### Geist Americas

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

### Geist Europe

+44 (0) 1823.275100  
geistglobal.com

### Geist Asia

China  
+86.755.86639505  
geistglobal.com

Shipped Weight

9lbs (4.08kg)

**Geist Americas**

800.432.3219  
[geistglobal.com](http://geistglobal.com)

Geist DCIM  
1.877.449.4150  
[geistglobal.com](http://geistglobal.com)

**Geist Europe**

+44 (0) 1823.275100  
[geistglobal.com](http://geistglobal.com)

**Geist Asia**

China  
+86.755.86639505  
[geistglobal.com](http://geistglobal.com)