

13648

Model Number: SPFCN104-10
Category: Metered
Sub Category: Surge
Power Configuration: 15A, 120V, 1.4kW
Physical Configuration: 19in / 483mm, Horizontal



Description: 13648 is a surge-protected PDU equipped with a local power meter displaying real-time power metrics. This metered PDU is ideal for environments lacking facility-level surge suppression or for applications requiring additional protection.

Product Summary: 13648 - Metered, Surge, 15A, 120V, Horizontal, (10) NEMA 5-15R, breakered, 10 ft power cord with 5-15P, Power - Local (A, V, W, PF)
 Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input. Black Powder Coat.

Monitoring: Power - Local (A, V, W, PF)
 Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input

Plug Form:



5-15P

Receptacle:



NEMA 5-15R
 (Quantity: 10)

Chassis Colors Options:



To discuss color options, contact your local sales representative.

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Product Specification and Options:

Monitoring	Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Monitoring Level 1	Aggregate - Total Unit Monitoring
Quantity Of Inputs	1
Voltage	120V
Current	15A
VA per Input (Load Capacity)	1.4kW
Frequency	50/60Hz
Over Current Protection	15A Thermal Breaker
Switch	No
Indicators - LED(s)	1 - Power ON Green LED
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA 5-15P
Receptacle/Socket Type #1	NEMA 5-15R
- Quantity on Face	10
- Quantity per Breaker	10
- Style	Duplex
- Maximum Output per Receptacle/Socket	15A
- Voltage per Receptacle/Socket	120V
Joule Rating	720
Maximum Clamping Voltage	340V
Response Time	< 5 nanoseconds
Technology Used	Super MOVs
Surge Indicator Red LED	Yes
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	19in / 483mm Horizontal Rackmount
Adjustable Mount Brackets	Yes
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Connected Equipment Warranty	5 years / \$5,000
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (HxWxD)	1.72in x 17in x 4.50in
Shipped Weight	7lbs (3.18kg)

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com