

I10162

Model Number: MN01X4B0-42IZ63-2PS56B0A10-S
Category: Basic
Sub Category: Upgradeable
Power Configuration: 20A, 230/400V WYE, 11.0kW
Physical Configuration: 66in / 1683mm, Vertical



Description: I10162 provides reliable power distribution where you need it in the rack. With the Geist Upgradeable hot-swap technology, users may easily transform basic PDUs to metered or monitored PDUs with the addition of the appropriate Interchangeable Monitoring Device (IMD) module; all without causing any interruption.

Product Summary: I10162 - Basic, Upgradeable, 20A, 230/400V WYE, 3 Phase, Vertical, (36) IEC C13, (6) IEC C19, 10 ft power cord with 3P+N+E (IP44), No Monitoring (Upgradeable with IMD module). Black Powder Coat.

Monitoring: No Monitoring (Upgradeable with IMD module)

Plug Form:



3P+N+E (IP44)

Receptacle:



IEC C13
(Quantity: 36)



IEC C19
(Quantity: 6)

Chassis Colors Options:



To discuss color options, contact your local sales representative.

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Product Specification and Options:

Monitoring	No Monitoring (Upgradeable with IMD module)
Quantity Of Inputs	1
Voltage	230/400V WYE
Current	20A x 3 Phase WYE
VA per Input (Load Capacity)	11.0kW
Frequency	50/60Hz
Over Current Protection	None
Switch	No
Power Cable Wire Gauge	12/5
Power Cable Length	10ft
Power Entry Location	Bottom Front
Plug Type	IEC60309 3P + N + E, 20A, 230/400V, Splashproof IP44
Combined Total Receptacle/Socket Quantity	42
Receptacle/Socket Type #1	IEC C13
- Quantity on Face	36
- Quantity per Phase	12
- Style	Banks of 6
- Voltage per Receptacle/Socket	230V
Receptacle/Socket Type #2	IEC C19
- Quantity on Face	6
- Quantity per Phase	2
- Style	Individual
- Voltage per Receptacle/Socket	230V
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	66in / 1683mm Vertical Rackmount
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	66.25in x 2.0in x 2.0in
Shipped Weight	16lbs (7.26kg)

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com