

## 38314

**Model Number:** VSSLN084-102S20  
**Category:** Basic  
**Sub Category:** Surge  
**Power Configuration:** 20A, 120V, 1.9kW  
**Physical Configuration:** 17in / 432mm, Horizontal/Vertical



**Description:** 38314 comes equipped with built-in surge protection. This basic power distribution unit is ideal for environments lacking facility-level surge suppression or for applications requiring additional protection.

**Product Summary:** 38314 - Basic, Surge, 20A, 120V, Horizontal/Vertical, (8) NEMA 5-20R, breaker, 10 ft power cord with 5-20P, Black Powder Coat.

**Plug Form:**



5-20P

**Receptacle:**



NEMA 5-20R  
(Quantity: 8)

**Chassis Colors Options:**



*To discuss color options, contact your local sales representative.*

## Product Specification and Options:

Quantity Of Inputs	1
Voltage	120V
Current	20A
VA per Input (Load Capacity)	1.9kW
Frequency	50/60Hz
Over Current Protection	20A Thermal Breaker
Switch	No
Indicators - LED(s)	1 - Power ON Green LED
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA 5-20P
Receptacle/Socket Type #1	NEMA 5-20R
- Quantity on Face	8
- Quantity per Breaker	8
- Style	Individual - In-Line
- Maximum Output per Receptacle/Socket	20A
- Voltage per Receptacle/Socket	120V
Center to Center Receptacle Spacing	1.25
Joule Rating	720
Maximum Clamping Voltage	340V
Response Time	< 5 nanoseconds
Technology Used	Super MOVs
Surge Indicator Red LED	Yes
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	17in / 432mm Vertical/Horizontal Rackmount
19in Panel Mount Brackets	Yes
Plastic Mounting Clips	1 - Bottom; 1 - Top
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Connected Equipment Warranty	5 years / \$5,000
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	17.00in x 1.61in x 1.61in
Shipped Weight	4lbs (1.81kg)

### Geist Americas

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

### Geist Europe

+44 (0) 1823.275100  
geistglobal.com

### Geist Asia

China  
+86.755.86639505  
geistglobal.com