

## I10107L

**Model Number:** MN01X1R1-06L198-4CS15A0H10-S  
**Category:** Basic  
**Sub Category:** Upgradeable  
**Power Configuration:** 35A, 208V DELTA, 10.0kW  
**Physical Configuration:** 19in / 483mm, Horizontal



**Description:**

I10107L provides reliable power distribution where you need it in the rack. With the Geist Upgradeable hot-swap technology, users may easily transform basic PDUs to metered or monitored PDUs with the addition of the appropriate Interchangeable Monitoring Device (IMD) module; all without causing any interruption.

**Product Summary:**

I10107L - Basic, Upgradeable, 35A, 208V DELTA, 3 Phase, Horizontal, (6) Locking IEC C19, breakered, 10 ft power cord with 3P+E CA, No Monitoring (Upgradeable with IMD module). Black Powder Coat.

**Monitoring:**

No Monitoring (Upgradeable with IMD module)

**Plug Form:**



3P+E CA

**Receptacle:**



Locking IEC C19  
(Quantity: 6)

**Chassis Colors Options:**



*To discuss color options, contact your local sales representative.*

**Geist Americas**

800.432.3219  
[geistglobal.com](http://geistglobal.com)

Geist DCIM  
1.877.449.4150  
[geistglobal.com](http://geistglobal.com)

**Geist Europe**

+44 (0) 1823.275100  
[geistglobal.com](http://geistglobal.com)

**Geist Asia**

China  
+86.755.86639505  
[geistglobal.com](http://geistglobal.com)

## Product Specification and Options:

Monitoring	No Monitoring (Upgradeable with IMD module)
Quantity Of Inputs	1
Voltage	208V Delta
Current	35A x 3 Phase DELTA
VA per Input (Load Capacity)	10.0kW
Frequency	50/60Hz
Over Current Protection	(3) 20A Double Pole Magnetic Breakers
Switch	Breaker/Switch Combination
Power Cable Wire Gauge	8/4
Power Cable Length	10ft
Power Entry Location	Left Rear
Plug Type	California Style 50A, 250V, 3P/4W Twistlock
Receptacle/Socket Type #1	U-Lock IEC C19
- Quantity on Rear	6
- Quantity per Breaker and Phase Combination	2
- U-Lock Color ID	3 Circuit = Orange, Green, Blue
- Style	Individual
- Voltage per Receptacle/Socket	208V
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	1U
Adjustable Mount Brackets	Yes
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (HxWxD)	1.72in x 17in x 8.5in
Shipped Weight	17lbs (7.71kg)