

## 38100

**Model Number:** SPFN104-1025  
**Category:** Basic  
**Sub Category:** Surge  
**Power Configuration:** 20A, 120V, 1.9kW  
**Physical Configuration:** 19in / 483mm, Horizontal



**Description:** 38100 comes equipped with built-in surge protection. This basic power distribution unit is ideal for environments lacking facility-level surge suppression or for applications requiring additional protection.

**Product Summary:** 38100 - Basic, Surge, 20A, 120V, Horizontal, (10) NEMA 5-20R, breakered, 10 ft power cord with 5-20P, Black Powder Coat.

**Plug Form:**



5-20P

**Receptacle:**



NEMA 5-20R  
(Quantity: 10)

**Chassis Colors Options:**



*To discuss color options, contact your local sales representative.*

## Product Specification and Options:

|  |   |
|--|---|
| Quantity Of Inputs                     | 1   |
| Voltage                                | 120V  |
| Current                                | 20A   |
| VA per Input (Load Capacity)           | 1.9kW   |
| Frequency                              | 50/60Hz   |
| Over Current Protection                | 20A Thermal Breaker   |
| Switch                                 | No  |
| Indicators - LED(s)                    | 1 - Power ON Green LED  |
| Power Cable Wire Gauge                 | 12/3  |
| Power Cable Length                     | 10ft  |
| Plug Type                              | NEMA 5-20P  |
| Receptacle/Socket Type #1              | NEMA 5-20R  |
| - Quantity on Face                     | 10  |
| - Quantity per Breaker                 | 10  |
| - Style                                | Duplex  |
| - Maximum Output per Receptacle/Socket | 20A   |
| - Voltage per Receptacle/Socket        | 120V  |
| Joule Rating                           | 720   |
| Maximum Clamping Voltage               | 340V  |
| Response Time                          | < 5 nanoseconds   |
| Technology Used                        | Super MOVs  |
| Surge Indicator Red LED                | Yes   |
| Continuous Operating Temperature Range | 10-45C / 50-113F  |
| Heavy Steel - Powder Coat Finish       | Black   |
| Configuration                          | 19in / 483mm Horizontal Rackmount   |
| Adjustable Mount Brackets              | Yes   |
| Made in the USA                        | Yes   |
| Product Warranty                       | 5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years |
| Connected Equipment Warranty           | 5 years / \$5,000   |
| Certification/Agency Approvals         | RoHS Compliant  |
| Certification/Agency Approvals         | UL & c-UL Listed 60950  |
| Chassis Dimensions (HxWxD)             | 1.72in x 17in x 4.50in  |
| Shipped Weight                         | 7lbs (3.18kg)   |

### Geist Americas

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

### Geist Europe

+44 (0) 1823.275100  
geistglobal.com

### Geist Asia

China  
+86.755.86639505  
geistglobal.com