

27986

Model Number: BRECN162-0020/16
Category: Metered
Sub Category: Standard
Power Configuration: 20A, 120V OR 208V, 1.9 or 3.3kW
Physical Configuration: 19in / 483mm, Horizontal



Description: The 27986 is a PDU equipped with a local power meter displaying real-time power metrics. This metered PDU is ideal for installations in facilities with proper surge protection at the main electrical service entrance.

Product Summary: 27986 - Metered, Standard, 20A, 120/208V, Horizontal, (16) IEC C13, C20, Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input. Black Powder Coat.

Monitoring: Power - Local (A, V, W, PF)
 Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input

Plug Form:



C20

Receptacle:



IEC C13
(Quantity: 16)

Chassis Colors Options:



Geist Americas

800.432.3219
 geistglobal.com

Geist DCIM
 1.877.449.4150
 geistglobal.com

Geist Europe

+44 (0) 1823.275100
 geistglobal.com

Geist Asia

China
 +86.755.86639505
 geistglobal.com

To discuss color options, contact your local sales representative.

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Product Specification and Options:

Monitoring	Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Monitoring Level 1	Aggregate - Total Unit Monitoring
Quantity Of Inputs	1
Voltage	120V or 208V
Current	20A
VA per Input (Load Capacity)	1.9 or 3.3kW
Frequency	50/60Hz
Over Current Protection	None
Switch	No
Plug Type	IEC60320 C20 Power Inlet (cord sold separately)
Receptacle/Socket Type #1	IEC C13
- Quantity on Face	4
- Quantity on Rear	12
- Style	1 Bank of 4; 2 Banks of 6
- Maximum Output per Receptacle/Socket	15A per receptacle bank
- Voltage per Receptacle/Socket	120V or 208V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	19in / 483mm Horizontal Rackmount
Adjustable Mount Brackets	Yes
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (HxWxD)	1.72in x 17in x 6.50in
Shipped Weight	4lbs (1.81kg)

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com