

## 27959

**Model Number:** BRELCN102-0020/16  
**Category:** Metered  
**Sub Category:** Standard  
**Power Configuration:** 20A, 120V OR 208V, 1.9 or 3.3kW  
**Physical Configuration:** 17in / 432mm, Horizontal/Vertical



**Description:** The 27959 is a PDU equipped with a local power meter displaying real-time power metrics. This metered PDU is ideal for installations in facilities with proper surge protection at the main electrical service entrance.

**Product Summary:** 27959 - Metered, Standard, 20A, 120/208V, Horizontal/Vertical, (10) IEC C13, C20, Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input. Black Powder Coat.

**Monitoring:** Power - Local (A, V, W, PF)  
 Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input

**Plug Form:**



C20

**Receptacle:**



IEC C13  
(Quantity: 10)

**Chassis Colors Options:**



*To discuss color options, contact your local sales representative.*

## Product Specification and Options:

Monitoring	Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Monitoring Level 1	Aggregate - Total Unit Monitoring
Quantity Of Inputs	1
Voltage	120V or 208V
Current	20A
VA per Input (Load Capacity)	1.9 or 3.3kW
Frequency	50/60Hz
Over Current Protection	None
Switch	No
Plug Type	IEC60320 C20 Power Inlet (cord sold separately)
Receptacle/Socket Type #1	IEC C13
- Quantity on Face	10
- Style	1 Bank of 4; 1 Bank of 6
- Maximum Output per Receptacle/Socket	15A per receptacle bank
- Voltage per Receptacle/Socket	120V or 208V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	17in / 432mm Vertical/Horizontal Rackmount
19in Panel Mount Brackets	Yes
SLB-4 Brackets	Yes
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	17.00in x 1.72in x 1.61in
Shipped Weight	2lbs (0.91kg)

### Geist Americas

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

### Geist Europe

+44 (0) 1823.275100  
geistglobal.com

### Geist Asia

China  
+86.755.86639505  
geistglobal.com