

I10098L

Model Number: MN01D9W1-48MI18-6PS6D0A10-S
Category: Metered
Sub Category: Upgradeable
Power Configuration: 60A, 208V, 9.9kW
Physical Configuration: 72in / 1829mm, Vertical



Description: The I10098L provides real-time power metrics to help prevent overloads and safely optimize load levels. Using Visible Light Communication (VLC) technology, I10098L optically transmits power usage data from its LED display to a handheld device over the Geist Mobile App, presenting comprehensive real-time power usage data down to the phase and circuit levels. With the Geists Upgradeable hot-swap technology, users may easily transform Metered PDUs to Monitored by replacing the Interchangeable Monitoring Device (IMD) module, without causing any interruption.

Product Summary: I10098L - Metered, Upgradeable, 60A, 208V, Vertical, (42) Locking IEC C13, (6) Locking IEC C19, breakered, 10 ft power cord with 2P+E (IP67), Input and Breaker level current monitoring. Local high visibility LED display. Input power monitoring available via VLC feature using the Geist app. Black Powder Coat.

Monitoring: Input and Breaker level current monitoring. Local high visibility LED display. Input power monitoring available via VLC feature using the Geist app.

Plug Form:



2P+E (IP67)

Receptacle:



Locking IEC C13
(Quantity: 42)



Locking IEC C19
(Quantity: 6)

Chassis Colors Options:



To discuss color options, contact your local sales representative.

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Product Specification and Options:

Monitoring	Input and Breaker level current monitoring. Local high visibility LED display. Input power monitoring available via VLC feature using the Geist app.
Monitoring Level 1	Phase (A) Monitoring (kWh, W, VA, PF, V, A) Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
Monitoring Level 2	Circuit / Breaker Monitoring (A) Circuit/Breaker Current Measurements Independently Tested and Verified at 2% Accuracy
VLC Support	Yes
Quantity Of Inputs	1
Voltage	208V
Current	60A
VA per Input (Load Capacity)	9.9kW
Frequency	50/60Hz
Over Current Protection	(3) 20A Double Pole Magnetic Breakers
Switch	Breaker/Switch Combination
Scrolling / Rotatable Digital Display	Yes
Power Cable Wire Gauge	6/3
Power Cable Length	10ft
Power Entry Location	Bottom Front
Plug Type	IEC60309 2P + E, 60A, Watertight IP67
Combined Total Receptacle/Socket Quantity	48
Receptacle/Socket Type #1	U-Lock IEC C13
- Quantity on Face	42
- Quantity per Breaker	14
- U-Lock Color ID	3 Circuit = Orange, Green, Blue
- Style	Individual
- Voltage per Receptacle/Socket	208V
Receptacle/Socket Type #2	U-Lock IEC C19
- Quantity on Face	6
- Quantity per Breaker	2
- U-Lock Color ID	3 Circuit = Orange, Green, Blue
- Style	Individual
- Voltage per Receptacle/Socket	208V
Internal RMS Voltage Sensor	Yes
Internal RMS Current Sensor	Yes
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Configuration	72in / 1829mm Vertical Rackmount
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	72in x 3.75in x3.44in
Shipped Weight	30lbs (13.61kg)

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com