

## I10161L

**Model Number:** MN01X4B0-30PN63-2PS56B0A10-S-A  
**Category:** Basic  
**Sub Category:** Upgradeable  
**Power Configuration:** 20A, 230/400V WYE, 11.0kW  
**Physical Configuration:** 66in / 1683mm, Vertical



**Description:** I10161L provides reliable power distribution where you need it in the rack. With the Geist Upgradeable hot-swap technology, users may easily transform basic PDUs to metered or monitored PDUs with the addition of the appropriate Interchangeable Monitoring Device (IMD) module; all without causing any interruption.

**Product Summary:** I10161L - Basic, Upgradeable, 20A, 230/400V WYE, 3 Phase, Vertical, (24) Locking IEC C13, (6) Locking IEC C19, Alternating Phase/Circuits, 10 ft power cord with 3P+N+E (IP44), No Monitoring (Upgradeable with IMD module). Black Powder Coat.


**Monitoring:** No Monitoring (Upgradeable with IMD module)

**Plug Form:**



3P+N+E (IP44)

**Receptacle:**



Locking IEC C13  
(Quantity: 24)



Locking IEC C19  
(Quantity: 6)

**Chassis Colors Options:**



*To discuss color options, contact your local sales representative.*

**Geist Americas**

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

**Geist Europe**

+44 (0) 1823.275100  
geistglobal.com

**Geist Asia**

China  
+86.755.86639505  
geistglobal.com

## Product Specification and Options:

Monitoring	No Monitoring (Upgradeable with IMD module)
Quantity Of Inputs	1
Voltage	230/400V WYE
Current	20A x 3 Phase WYE
VA per Input (Load Capacity)	11.0kW
Frequency	50/60Hz
Over Current Protection	None
Switch	No
Power Cable Wire Gauge	12/5
Power Cable Length	10ft
Power Entry Location	Bottom Front
Plug Type	IEC60309 3P + N + E, 20A, 230/400V, Splashproof IP44
Combined Total Receptacle/Socket Quantity	30
Alternating Phase/Circuits	Yes
Receptacle/Socket Type #1	U-Lock IEC C13
- Quantity on Face	24
- Quantity per Phase	8
- U-Lock Color ID	3 Circuit = Orange, Green, Blue
- Style	Individual
- Voltage per Receptacle/Socket	230V
Receptacle/Socket Type #2	U-Lock IEC C19
- Quantity on Face	6
- Quantity per Phase	2
- U-Lock Color ID	3 Circuit = Orange, Green, Blue
- Style	Individual
- Voltage per Receptacle/Socket	230V
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	66in / 1683mm Vertical Rackmount
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	RoHS Compliant

### Geist Americas

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

### Geist Europe

+44 (0) 1823.275100  
geistglobal.com

### Geist Asia

China  
+86.755.86639505  
geistglobal.com

Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	66.25in x 2.0in x 2.0in
Shipped Weight	16lbs (7.26kg)

#### Geist Americas

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

#### Geist Europe

+44 (0) 1823.275100  
geistglobal.com

#### Geist Asia

China  
+86.755.86639505  
geistglobal.com