

I10027L

Model Number: MN01X9W1-42PTB3-5PS56B0A10-S
Category: Basic
Sub Category: Upgradeable
Power Configuration: 40A, 230/400V WYE, 27.6kW
Physical Configuration: 72in / 1829mm, Vertical



Description: I10027L provides reliable power distribution where you need it in the rack. With the Geist Upgradeable hot-swap technology, users may easily transform basic PDUs to metered or monitored PDUs with the addition of the appropriate Interchangeable Monitoring Device (IMD) module; all without causing any interruption.

Product Summary: I10027L - Basic, Upgradeable, 40A, 230/400V WYE, 3 Phase, Vertical, (30) Locking IEC C13, (12) Locking IEC C19, breaker, 10 ft power cord with 3P+N+E (IP44), No Monitoring (Upgradeable with IMD module). Black Powder Coat.


Monitoring: No Monitoring (Upgradeable with IMD module)

Plug Form:



3P+N+E (IP44)

Receptacle:



Locking IEC C13
(Quantity: 30)



Locking IEC C19
(Quantity: 12)

Chassis Colors Options:



To discuss color options, contact your local sales representative.

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Product Specification and Options:

Monitoring	No Monitoring (Upgradeable with IMD module)
Quantity Of Inputs	1
Voltage	230/400V WYE
Current	40A x 3 Phase WYE
VA per Input (Load Capacity)	27.6kW
Frequency	50/60Hz
Over Current Protection	(6) 20A Single Pole Magnetic Breakers
Switch	Breaker/Switch Combination
Power Cable Wire Gauge	4/5
Power Cable Length	10ft
Power Entry Location	Bottom Front
Plug Type	IEC60309 3P + N + E, 60A, 230/400V, Splashproof IP44
Combined Total Receptacle/Socket Quantity	42
Receptacle/Socket Type #1	U-Lock IEC C13
- Quantity on Face	30
- Quantity per Breaker	5
- Quantity per Phase	10
- U-Lock Color ID	6 Circuit = Orange, Green, Blue, Light Orange, Light Green, Light Blue
- Style	Individual
- Voltage per Receptacle/Socket	230V
Receptacle/Socket Type #2	U-Lock IEC C19
- Quantity on Face	12
- Quantity per Breaker	2
- Quantity per Phase	4
- U-Lock Color ID	6 Circuit = Orange, Green, Blue, Light Orange, Light Green, Light Blue
- Style	Individual
- Voltage per Receptacle/Socket	230V
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	72in / 1829mm Vertical Rackmount
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	FCC Part 15 Class A Conformance

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	72in x 3.75in x3.44in
Shipped Weight	39lbs (17.69kg)

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com