

## I10002

**Model Number:** MN01X4B1-24D203-3TL5A0A10-S  
**Category:** Basic  
**Sub Category:** Upgradeable  
**Power Configuration:** 30A, 120V, 2.8kW  
**Physical Configuration:** 66in / 1683mm, Vertical



**Description:** I10002 provides reliable power distribution where you need it in the rack. With the Geist Upgradeable hot-swap technology, users may easily transform basic PDUs to metered or monitored PDUs with the addition of the appropriate Interchangeable Monitoring Device (IMD) module; all without causing any interruption.

**Product Summary:** I10002 - Basic, Upgradeable, 30A, 120V, Vertical, (24) NEMA 5-20R, breakerless, 10 ft power cord with L5-30P, No Monitoring (Upgradeable with IMD module). Black Powder Coat.

**Monitoring:** No Monitoring (Upgradeable with IMD module)

**Plug Form:**



L5-30P

**Receptacle:**



NEMA 5-20R  
(Quantity: 24)

**Chassis Colors Options:**



*To discuss color options, contact your local sales representative.*

## Product Specification and Options:

Monitoring	No Monitoring (Upgradeable with IMD module)
Quantity Of Inputs	1
Voltage	120V
Current	30A
VA per Input (Load Capacity)	2.8kW
Frequency	50/60Hz
Over Current Protection	(2) 20A Single Pole Magnetic Breakers
Switch	Breaker/Switch Combination
Power Cable Wire Gauge	10/3
Power Cable Length	10ft
Power Entry Location	Bottom Front
Plug Type	NEMA L5-30P Twistlock
Receptacle/Socket Type #1	NEMA 5-20R
- Quantity on Face	24
- Quantity per Breaker	12
- Style	Duplex
- Voltage per Receptacle/Socket	120V
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	66in / 1683mm Vertical Rackmount
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	66.25in x 2.0in x 2.0in
Shipped Weight	16lbs (7.26kg)

### Geist Americas

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

### Geist Europe

+44 (0) 1823.275100  
geistglobal.com

### Geist Asia

China  
+86.755.86639505  
geistglobal.com