

28052

Model Number: BREC160-0020/16
Category: Metered
Sub Category: Standard
Power Configuration: 20A, 120V OR 208V, 1.9 or 3.3kW
Physical Configuration: 19in / 483mm, Horizontal



Description: The 28052 is a PDU equipped with a local power meter displaying real-time power metrics. This metered PDU is ideal for installations in facilities with proper surge protection at the main electrical service entrance.

Product Summary: 28052 - Metered, Standard, 20A, 120/208V, Horizontal, (16) IEC C13, breakered, C20, Power - Local (A, V, W, PF)
 Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input. Black Powder Coat.

Monitoring: Power - Local (A, V, W, PF)
 Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input

Plug Form:



C20

Receptacle:



IEC C13
(Quantity: 16)

Chassis Colors Options:

Geist Americas

800.432.3219
 geistglobal.com

Geist DCIM
 1.877.449.4150
 geistglobal.com

Geist Europe

+44 (0) 1823.275100
 geistglobal.com

Geist Asia

China
 +86.755.86639505
 geistglobal.com



To discuss color options, contact your local sales representative.

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Product Specification and Options:

| | |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------|
| Monitoring | Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input |
| Monitoring Level 1 | Aggregate - Total Unit Monitoring |
| Quantity Of Inputs | 1 |
| Voltage | 120V or 208V |
| Current | 20A |
| VA per Input (Load Capacity) | 1.9 or 3.3kW |
| Frequency | 50/60Hz |
| Over Current Protection | 20A Double Pole Magnetic Breaker |
| Switch | Breaker/Switch Combination |
| Plug Type | IEC60320 C20 Power Inlet (cord sold separately) |
| Receptacle/Socket Type #1 | IEC C13 |
| - Quantity on Face | 4 |
| - Quantity on Rear | 12 |
| - Quantity per Breaker | 16 |
| - Style | 1 Bank of 4; 2 Banks of 6 |
| - Maximum Output per Receptacle/Socket | 15A per receptacle bank |
| - Voltage per Receptacle/Socket | 120V or 208V |
| Continuous Operating Temperature Range | 10-45C / 50-113F |
| Heavy Steel - Powder Coat Finish | Black |
| Configuration | 19in / 483mm Horizontal Rackmount |
| Adjustable Mount Brackets | Yes |
| Made in the USA | Yes |
| Product Warranty | 5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years |
| Certification/Agency Approvals | RoHS Compliant |
| Certification/Agency Approvals | UL & c-UL Listed 60950 |
| Chassis Dimensions (HxWxD) | 1.72in x 17in x 6.50in |
| Shipped Weight | 4lbs (1.81kg) |

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com