

## I10103L

**Model Number:** MN01X1R1-10L138-3TL6A0H10-S  
**Category:** Basic  
**Sub Category:** Upgradeable  
**Power Configuration:** 30A, 208V, 4.9kW  
**Physical Configuration:** 19in / 483mm, Horizontal



**Description:** I10103L provides reliable power distribution where you need it in the rack. With the Geist Upgradeable hot-swap technology, users may easily transform basic PDUs to metered or monitored PDUs with the addition of the appropriate Interchangeable Monitoring Device (IMD) module; all without causing any interruption.

**Product Summary:** I10103L - Basic, Upgradeable, 30A, 208V, Horizontal, (10) Locking IEC C13, breakered, 10 ft power cord with L6-30P, No Monitoring (Upgradeable with IMD module). Black Powder Coat.

**Monitoring:** No Monitoring (Upgradeable with IMD module)

**Plug Form:**



L6-30P

**Receptacle:**



Locking IEC C13  
(Quantity: 10)

**Chassis Colors Options:**



**Geist Americas**

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

**Geist Europe**

+44 (0) 1823.275100  
geistglobal.com

**Geist Asia**

China  
+86.755.86639505  
geistglobal.com

*To discuss color options, contact your local sales representative.*

**Geist Americas**

800.432.3219  
[geistglobal.com](http://geistglobal.com)

Geist DCIM  
1.877.449.4150  
[geistglobal.com](http://geistglobal.com)

**Geist Europe**

+44 (0) 1823.275100  
[geistglobal.com](http://geistglobal.com)

**Geist Asia**

China  
+86.755.86639505  
[geistglobal.com](http://geistglobal.com)

## Product Specification and Options:

Monitoring	No Monitoring (Upgradeable with IMD module)
Quantity Of Inputs	1
Voltage	208V
Current	30A
VA per Input (Load Capacity)	4.9kW
Frequency	50/60Hz
Over Current Protection	(2) 20A Double Pole Magnetic Breakers
Switch	Breaker/Switch Combination
Power Cable Wire Gauge	10/3
Power Cable Length	10ft
Power Entry Location	Left Rear
Plug Type	NEMA L6-30P Twistlock
Receptacle/Socket Type #1	U-Lock IEC C13
- Quantity on Rear	10
- Quantity per Breaker	5
- U-Lock Color ID	2 Circuit = Orange, Green
- Style	Individual
- Voltage per Receptacle/Socket	208V
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	1U
Adjustable Mount Brackets	Yes
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (HxWxD)	1.72in x 17in x 8.5in
Shipped Weight	12lbs (5.44kg)

### Geist Americas

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

### Geist Europe

+44 (0) 1823.275100  
geistglobal.com

### Geist Asia

China  
+86.755.86639505  
geistglobal.com