

38252

Model Number: VHVBN242-102C13TL6

Category:BasicSub Category:Standard

Power Configuration: 20A, 208V, 3.3kW **Physical Configuration:** 66in / 1683mm, Vertical



Description: The 38252 functions as a basic power strip without built-in surge protection. This unit is ideal for installations

in facilities with proper surge protection at the main electrical service entrance.

Product Summary: 38252 - Basic, Standard, 20A, 208V, Vertical, (24) IEC C13, 10 ft power cord with L6-20P, Black Powder Coat.

Plug Form:



L6-20P

Receptacle:



IEC C13 (Quantity: 24)

Chassis Colors Options:



To discuss color options, contact your local sales representative.

Geist Asia



Product Specification and Options:

Quantity Of Inputs	1
Voltage	208V
Current	20A
VA per Input (Load Capacity)	3.3kW
Frequency	50/60Hz
Over Current Protection	None
Switch	No
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA L6-20P Twistlock
Receptacle/Socket Type #1	IEC C13
- Quantity on Face	24
- Style	Banks of 4
- Maximum Output per Receptacle/Socket	15A per receptacle bank
- Voltage per Receptacle/Socket	208V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	66in / 1683mm Vertical Rackmount
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	66.25in x 1.72in x 1.61in
Shipped Weight	13lbs (5.9kg)