

11060

Model Number:	2VHVRN062-102L20TL6
Category:	Basic
Sub Category:	Standard
Power Configuration:	20A, 208V, 3.3kW
Physical Configuration:	2U 19in / 483mm, Horizontal



Description: The 11060 functions as a basic power strip without built-in surge protection. This unit is ideal for installations in facilities with proper surge protection at the main electrical service entrance.

Product Summary: 11060 - Basic, Standard, 20A, 208V, Horizontal, (6) NEMA L6-20R, 10 ft power cord with L6-20P, Black Powder Coat.

Plug Form:



L6-20P

Receptacle:



NEMA L6-20R
(Quantity: 6)

Chassis Colors Options:



To discuss color options, contact your local sales representative.

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Product Specification and Options:

Quantity Of Inputs	1
Voltage	208V
Current	20A
VA per Input (Load Capacity)	3.3kW
Frequency	50/60Hz
Over Current Protection	None
Switch	No
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA L6-20P Twistlock
Receptacle/Socket Type #1	NEMA L6-20R
- Quantity on Rear	6
- Style	Individual
- Maximum Output per Receptacle/Socket	20A
- Voltage per Receptacle/Socket	208V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	19in / 483mm Horizontal Rackmount
19in Recess Mount	Yes
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (HxWxD)	3.39in x 17in x 6in
Shipped Weight	14lbs (6.35kg)

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com